

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249364

Luminaire Tested: P3AS13R509027DE010 E3D1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249364
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-32)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R509027DE010 E3D1MW
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 90CRI , E3D1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1241.9 lumens
Efficiency: N/A
Efficacy: 85.1 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249364

CATALOG NUMBER: P3AS13R509027DE010 E3D1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1249364

CATALOG NUMBER: P3AS13R509027DE010 E3D1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	97	97	97	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	85
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	82	82	80
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	77	77	76
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	70	70	69
8	85	76	71	67	83	76	71	67	75	70	67	74	70	67	73	69	66	66	66	65
9	81	73	68	64	80	72	67	64	71	67	64	71	66	63	70	66	63	63	63	62
10	78	69	64	61	77	69	64	61	68	64	61	68	63	61	67	63	60	60	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	432553
5°	424806
10°	407897
15°	374032
20°	329822
25°	252789
30°	137439
35°	44223
40°	10391
45°	1395
50°	1228
55°	1376
60°	1184
65°	1401
70°	1154
75°	1525
80°	1137
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 85°
Luminance: 2264 cd/sqm

TEST NUMBER: P1249364

CATALOG NUMBER: P3AS13R509027DE010 E3D1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.1	14.6
10°-20°	458.0	36.9
20°-30°	458.7	36.9
30°-40°	129.0	10.4
40°-50°	7.8	0.6
50°-60°	2.9	0.2
60°-70°	2.3	0.2
70°-80°	1.5	0.1
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1097.8	88.4
0°-40°	1226.7	98.8
0°-60°	1237.4	99.6
0°-90°	1241.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1241.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1973	
5°	1930	181
15°	1648	458
25°	1045	459
35°	165	129
45°	4	8
55°	4	3
65°	3	2
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1249364

CATALOG NUMBER: P3AS13R509027DE010 E3D1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1972.6
2.5°	1962.6
5°	1929.9
7.5°	1885.4
10°	1831.9
12.5°	1751.1
15°	1647.6
17.5°	1528.7
20°	1413.4
22.5°	1270.0
25°	1044.8
27.5°	778.0
30°	542.8
32.5°	327.7
35°	165.2
37.5°	78.1
40°	36.3
42.5°	13.6
45°	4.5
47.5°	3.6
50°	3.6
52.5°	3.6
55°	3.6
57.5°	2.7
60°	2.7
62.5°	2.7
65°	2.7
67.5°	1.8
70°	1.8
72.5°	1.8
75°	1.8
77.5°	0.9
80°	0.9
82.5°	0.9
85°	0.9
87.5°	0.0
90°	0.0

(END OF REPORT)