

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249374

Luminaire Tested: P3AS13R509027DE010 E3DLD1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249374
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R509027DE010 E3DLD1H
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 90CRI , E3DLD1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 795.0 lumens
Efficiency: N/A
Efficacy: 54.4 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249374
CATALOG NUMBER: P3AS13R509027DE010 E3DLD1H

Luminous Intensity Polar Plot





TEST NUMBER: P1249374
 CATALOG NUMBER: P3AS13R509027DE010 E3DLD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	83			83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			75
4	93	85	78	73	91	83	77	73	81	76	72	79	75	71	77	73	70	69			69
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63			63
6	83	73	66	61	81	72	65	61	70	65	60	69	64	60	67	63	59	58			58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	53			53
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50			50
9	70	59	53	48	69	59	52	48	58	52	48	57	52	48	56	51	48	46			46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43			43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	161566
5°	159190
10°	152124
15°	140886
20°	126618
25°	111297
30°	94647
35°	76747
40°	57651
45°	37151
50°	17637
55°	13878
60°	13113
65°	12245
70°	11028
75°	9997
80°	9218
85°	9057

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 37151 cd/sqm



TEST NUMBER: P1249374
 CATALOG NUMBER: P3AS13R509027DE010 E3DLD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.8	8.5
10°-20°	173.0	21.8
20°-30°	210.2	26.4
30°-40°	178.3	22.4
40°-50°	92.6	11.6
50°-60°	33.4	4.2
60°-70°	23.1	2.9
70°-80°	12.6	1.6
80°-90°	3.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	451.1	56.7
0°-40°	629.3	79.2
0°-60°	755.4	95.0
0°-90°	795.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	795.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	737	
5°	723	68
15°	621	173
25°	460	210
35°	287	178
45°	120	93
55°	36	33
65°	24	23
75°	12	13
85°	4	4
90°	0	

TEST NUMBER: P1249374
CATALOG NUMBER: P3AS13R509027DE010 E3DLD1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	736.8
2.5°	734.0
5°	723.2
7.5°	706.8
10°	683.2
12.5°	653.3
15°	620.6
17.5°	583.4
20°	542.6
22.5°	500.9
25°	460.0
27.5°	417.4
30°	373.8
32.5°	330.3
35°	286.7
37.5°	244.1
40°	201.4
42.5°	160.6
45°	119.8
47.5°	79.8
50°	51.7
52.5°	39.9
55°	36.3
57.5°	32.7
60°	29.9
62.5°	26.3
65°	23.6
67.5°	20.0
70°	17.2
72.5°	14.5
75°	11.8
77.5°	9.1
80°	7.3
82.5°	5.4
85°	3.6
87.5°	1.8
90°	0.0

(END OF REPORT)