

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249383

Luminaire Tested: P3AS13R509027DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249383
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R509027DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1021.0 lumens
Efficiency: N/A
Efficacy: 69.9 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249383

CATALOG NUMBER: P3AS13R509027DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1249383

CATALOG NUMBER: P3AS13R509027DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	97	92	88	101	95	91	87	93	89	86		90	87	84		88
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		75
7	85	76	70	66	84	75	70	66	74	69	66		73	69	65		72
8	81	72	66	62	80	71	66	62	70	65	62		69	65	62		68
9	78	68	63	59	76	68	62	59	67	62	59		66	62	58		65
10	74	65	59	56	73	65	59	56	64	59	55		63	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	325062
5°	318511
10°	298347
15°	267084
20°	224766
25°	171542
30°	111486
35°	66093
40°	38186
45°	19134
50°	7130
55°	5543
60°	5175
65°	4722
70°	4680
75°	4575
80°	4546
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19134 cd/sqm

TEST NUMBER: P1249383

CATALOG NUMBER: P3AS13R509027DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.6	13.2
10°-20°	325.4	31.9
20°-30°	319.2	31.3
30°-40°	160.8	15.7
40°-50°	50.8	5.0
50°-60°	13.2	1.3
60°-70°	9.3	0.9
70°-80°	5.7	0.6
80°-90°	2.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	779.2	76.3
0°-40°	940.0	92.1
0°-60°	1003.9	98.3
0°-90°	1021.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1021.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1482	
5°	1447	135
15°	1176	325
25°	709	319
35°	247	161
45°	62	51
55°	14	13
65°	9	9
75°	5	6
85°	2	2
90°	0	

TEST NUMBER: P1249383

CATALOG NUMBER: P3AS13R509027DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1482.4
2.5°	1473.4
5°	1447.0
7.5°	1399.8
10°	1339.9
12.5°	1262.7
15°	1176.5
17.5°	1076.6
20°	963.2
22.5°	840.6
25°	709.0
27.5°	569.2
30°	440.3
32.5°	331.3
35°	246.9
37.5°	182.5
40°	133.4
42.5°	94.4
45°	61.7
47.5°	35.4
50°	20.9
52.5°	15.4
55°	14.5
57.5°	12.7
60°	11.8
62.5°	10.9
65°	9.1
67.5°	8.2
70°	7.3
72.5°	6.4
75°	5.4
77.5°	4.5
80°	3.6
82.5°	2.7
85°	1.8
87.5°	0.9
90°	0.0

(END OF REPORT)