

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250460

Luminaire Tested: P3AS24R559027D010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250460
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R559027D010 E3D1WH
Description: 3in Adjustable LED luminaire with, R55 optic, 2700K CCT AND, 90CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2333.0 lumens
Efficiency: N/A
Efficacy: 81.0 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250460
CATALOG NUMBER: P3AS24R559027D010 E3D1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1250460
 CATALOG NUMBER: P3AS24R559027D010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89	89	89	89
3	104	98	94	90	102	97	93	90	95	91	88	92	89	87	90	88	86	84	84	84	84
4	100	93	88	84	98	92	87	84	90	86	83	88	84	82	86	83	81	79	79	79	79
5	95	88	82	79	94	87	82	78	85	81	78	84	80	77	82	79	76	75	75	75	75
6	91	83	78	74	90	82	77	74	81	76	73	80	76	73	78	75	72	71	71	71	71
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67	67	67	67
8	83	75	69	66	82	74	69	66	73	69	65	72	68	65	71	68	65	63	63	63	63
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	64	61	60	60	60	60
10	77	68	62	59	76	67	62	59	67	62	59	66	62	59	65	61	58	57	57	57	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	676547
5°	652585
10°	675939
15°	666406
20°	616754
25°	498803
30°	298932
35°	101322
40°	27909
45°	12373
50°	3616
55°	688
60°	395
65°	467
70°	577
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12373 cd/sqm



TEST NUMBER: P1250460
 CATALOG NUMBER: P3AS24R559027D010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	286.8	12.3
10°-20°	817.3	35.0
20°-30°	908.5	38.9
30°-40°	282.8	12.1
40°-50°	33.9	1.5
50°-60°	2.6	0.1
60°-70°	0.9	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2012.6	86.3
0°-40°	2295.4	98.4
0°-60°	2332.0	100.0
0°-90°	2333.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2333.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3085	
5°	2965	287
15°	2936	817
25°	2062	908
35°	378	283
45°	40	34
55°	2	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1250460
CATALOG NUMBER: P3AS24R559027D010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3085.3
1°	3073.8
2°	3043.6
3°	3006.4
4°	2972.7
5°	2964.7
6°	2973.6
7°	2992.2
8°	3013.5
9°	3030.3
10°	3035.7
11°	3032.1
12°	3017.9
13°	2995.8
14°	2970.1
15°	2935.5
16°	2895.6
17°	2845.1
18°	2788.4
19°	2720.1
20°	2643.0
21°	2555.3
22°	2451.6
23°	2337.2
24°	2206.1
25°	2061.6
26°	1902.9
27°	1734.5
28°	1554.6
29°	1369.4
30°	1180.6
31°	990.9
32°	805.7
32.5°	723.2
33°	638.2
34°	493.7
35°	378.5
36°	288.1
37°	213.6
37.5°	182.6
38°	158.7
39°	120.5
40°	97.5
42.5°	62.0
45°	39.9



TEST NUMBER: P1250460
CATALOG NUMBER: P3AS24R559027D010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	23.9
50°	10.6
52.5°	3.5
55°	1.8
57.5°	0.9
60°	0.9
62.5°	0.9
65°	0.9
67.5°	0.9
70°	0.9
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)