

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249413

Luminaire Tested: P3AS13R559027DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249413
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R559027DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R55 optic, 2700K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 660.0 lumens
Efficiency: N/A
Efficacy: 45.2 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249413

CATALOG NUMBER: P3AS13R559027DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1249413

CATALOG NUMBER: P3AS13R559027DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		97
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85
4	96	88	82	77	94	87	81	77	84	80	76		82	78	75		80
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	78	68	62	57	76	67	61	57	66	61	57		65	60	57		64
9	74	64	58	54	73	63	58	54	62	57	53		62	57	53		61
10	70	60	55	51	69	60	54	50	59	54	50		58	54	50		58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	179547
5°	175038
10°	162722
15°	144904
20°	123141
25°	99369
30°	75758
35°	53886
40°	35552
45°	21087
50°	12383
55°	7608
60°	6754
65°	6123
70°	5257
75°	4575
80°	4546
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21087 cd/sqm

TEST NUMBER: P1249413

CATALOG NUMBER: P3AS13R559027DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.8	11.2
10°-20°	177.0	26.8
20°-30°	187.4	28.4
30°-40°	126.6	19.2
40°-50°	55.5	8.4
50°-60°	19.9	3.0
60°-70°	11.7	1.8
70°-80°	6.1	0.9
80°-90°	2.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	438.2	66.4
0°-40°	564.9	85.6
0°-60°	640.3	97.0
0°-90°	660.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	660.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	819	
5°	795	74
15°	638	177
25°	411	187
35°	201	127
45°	68	56
55°	20	20
65°	12	12
75°	5	6
85°	2	2
90°	0	

TEST NUMBER: P1249413

CATALOG NUMBER: P3AS13R559027DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	818.8
2.5°	812.4
5°	795.2
7.5°	767.1
10°	730.8
12.5°	687.3
15°	638.3
17.5°	583.9
20°	527.7
22.5°	468.8
25°	410.7
27.5°	353.6
30°	299.2
32.5°	247.5
35°	201.3
37.5°	159.6
40°	124.2
42.5°	93.4
45°	68.0
47.5°	49.9
50°	36.3
52.5°	25.4
55°	19.9
57.5°	18.1
60°	15.4
62.5°	13.6
65°	11.8
67.5°	10.0
70°	8.2
72.5°	7.3
75°	5.4
77.5°	4.5
80°	3.6
82.5°	2.7
85°	1.8
87.5°	0.9
90°	0.0

(END OF REPORT)