

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250468

Luminaire Tested: P3AS24R559027D010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250468
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R559027D010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R55 optic, 2700K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 750.0 lumens
Efficiency: N/A
Efficacy: 26.0 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250468
CATALOG NUMBER: P3AS24R559027D010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1250468
 CATALOG NUMBER: P3AS24R559027D010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91			
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82			
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74			
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68			
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	64	62			
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57			
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52			
8	73	62	55	51	72	62	55	51	60	55	50	59	54	50	58	53	50	48			
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45			
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	141019
5°	139225
10°	133732
15°	125086
20°	114110
25°	101812
30°	89052
35°	73990
40°	58309
45°	39570
50°	24187
55°	12540
60°	11666
65°	11052
70°	10194
75°	8981
80°	8966
85°	6793

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 39570 cd/sqm



TEST NUMBER: P1250468
 CATALOG NUMBER: P3AS24R559027D010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.3	7.9
10°-20°	154.0	20.5
20°-30°	192.8	25.7
30°-40°	172.2	23.0
40°-50°	100.8	13.4
50°-60°	34.8	4.6
60°-70°	21.0	2.8
70°-80°	11.7	1.6
80°-90°	3.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	406.2	54.2
0°-40°	578.3	77.1
0°-60°	713.9	95.2
0°-90°	750.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	750.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	643	
5°	632	59
15°	551	154
25°	421	193
35°	276	172
45°	128	101
55°	33	35
65°	21	21
75°	11	12
85°	3	3
90°	0	



TEST NUMBER: P1250468
CATALOG NUMBER: P3AS24R559027D010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	643.1
2.5°	639.6
5°	632.5
7.5°	618.3
10°	600.6
12.5°	578.4
15°	551.0
17.5°	521.7
20°	489.0
22.5°	455.3
25°	420.8
27.5°	386.2
30°	351.7
32.5°	314.5
35°	276.4
37.5°	239.2
40°	203.7
42.5°	165.6
45°	127.6
47.5°	97.4
50°	70.9
52.5°	46.1
55°	32.8
57.5°	29.2
60°	26.6
62.5°	23.9
65°	21.3
67.5°	18.6
70°	15.9
72.5°	13.3
75°	10.6
77.5°	8.9
80°	7.1
82.5°	4.4
85°	2.7
87.5°	1.8
90°	0.0

(END OF REPORT)