

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249427

Luminaire Tested: P3AS13R609027DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249427
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R609027DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R60 optic, 2700K CCT AND, 90CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 954.0 lumens
Efficiency: N/A
Efficacy: 65.3 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249427

CATALOG NUMBER: P3AS13R609027DE010 E3DL1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1249427

CATALOG NUMBER: P3AS13R609027DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		85
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		79
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		73
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		68
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		63
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		59
8	77	68	61	57	76	67	61	57	66	60	57		65	60	56		55
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		51
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	225267
5°	223134
10°	216629
15°	202952
20°	179636
25°	150275
30°	117765
35°	85447
40°	56849
45°	35415
50°	19172
55°	5543
60°	5175
65°	4722
70°	4680
75°	4575
80°	4546
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 35415 cd/sqm

TEST NUMBER: P1249427

CATALOG NUMBER: P3AS13R609027DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.5	10.0
10°-20°	248.0	26.0
20°-30°	282.7	29.6
30°-40°	200.5	21.0
40°-50°	91.0	9.5
50°-60°	19.3	2.0
60°-70°	9.3	1.0
70°-80°	5.7	0.6
80°-90°	2.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	626.2	65.6
0°-40°	826.7	86.7
0°-60°	937.0	98.2
0°-90°	954.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	954.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1027	
5°	1014	95
15°	894	248
25°	621	283
35°	319	200
45°	114	91
55°	14	19
65°	9	9
75°	5	6
85°	2	2
90°	0	

TEST NUMBER: P1249427

CATALOG NUMBER: P3AS13R609027DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1027.3
2.5°	1023.7
5°	1013.7
7.5°	996.5
10°	972.9
12.5°	939.4
15°	894.0
17.5°	836.9
20°	769.8
22.5°	697.3
25°	621.1
27.5°	543.1
30°	465.1
32.5°	390.8
35°	319.2
37.5°	255.7
40°	198.6
42.5°	150.5
45°	114.2
47.5°	85.2
50°	56.2
52.5°	26.3
55°	14.5
57.5°	12.7
60°	11.8
62.5°	10.9
65°	9.1
67.5°	8.2
70°	7.3
72.5°	6.3
75°	5.4
77.5°	4.5
80°	3.6
82.5°	2.7
85°	1.8
87.5°	0.9
90°	0.0

(END OF REPORT)