

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249441

Luminaire Tested: P3AS13R609027DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249441
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R609027DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R60 optic, 2700K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 954.0 lumens
Efficiency: N/A
Efficacy: 65.3 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249441

CATALOG NUMBER: P3AS13R609027DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1249441

CATALOG NUMBER: P3AS13R609027DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93		
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85		
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	80	79		
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73		
5	91	82	76	71	89	81	75	71	79	74	70	78	73	70	76	72	69	68		
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63		
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59		
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55		
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51		
10	70	60	54	50	69	60	54	50	59	53	50	58	53	50	57	53	49	48		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	225267
5°	223134
10°	216629
15°	202952
20°	179636
25°	150275
30°	117765
35°	85447
40°	56849
45°	35415
50°	19172
55°	5543
60°	5175
65°	4722
70°	4680
75°	4575
80°	4546
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 35415 cd/sqm

TEST NUMBER: P1249441

CATALOG NUMBER: P3AS13R609027DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.5	10.0
10°-20°	248.0	26.0
20°-30°	282.7	29.6
30°-40°	200.5	21.0
40°-50°	91.0	9.5
50°-60°	19.3	2.0
60°-70°	9.3	1.0
70°-80°	5.7	0.6
80°-90°	2.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	626.2	65.6
0°-40°	826.7	86.7
0°-60°	937.0	98.2
0°-90°	954.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	954.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1027	
5°	1014	95
15°	894	248
25°	621	283
35°	319	200
45°	114	91
55°	14	19
65°	9	9
75°	5	6
85°	2	2
90°	0	

TEST NUMBER: P1249441

CATALOG NUMBER: P3AS13R609027DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1027.3
2.5°	1023.7
5°	1013.7
7.5°	996.5
10°	972.9
12.5°	939.4
15°	894.0
17.5°	836.9
20°	769.8
22.5°	697.3
25°	621.1
27.5°	543.1
30°	465.1
32.5°	390.8
35°	319.2
37.5°	255.7
40°	198.6
42.5°	150.5
45°	114.2
47.5°	85.2
50°	56.2
52.5°	26.3
55°	14.5
57.5°	12.7
60°	11.8
62.5°	10.9
65°	9.1
67.5°	8.2
70°	7.3
72.5°	6.3
75°	5.4
77.5°	4.5
80°	3.6
82.5°	2.7
85°	1.8
87.5°	0.9
90°	0.0

(END OF REPORT)