

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250508

Luminaire Tested: P3AS24R609027D010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250508
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R609027D010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 2700K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1315.0 lumens
Efficiency: N/A
Efficacy: 45.7 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250508

CATALOG NUMBER: P3AS24R609027D010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1250508

CATALOG NUMBER: P3AS24R609027D010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	60	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		60
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	333263
5°	325775
10°	305004
15°	273645
20°	235314
25°	194576
30°	153745
35°	114171
40°	78633
45°	49307
50°	27121
55°	15904
60°	14253
65°	12193
70°	10450
75°	10675
80°	9092
85°	9057

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 49307 cd/sqm

TEST NUMBER: P1250508

CATALOG NUMBER: P3AS24R609027D010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.8	10.5
10°-20°	334.8	25.5
20°-30°	367.2	27.9
30°-40°	267.5	20.3
40°-50°	126.4	9.6
50°-60°	41.4	3.1
60°-70°	23.5	1.8
70°-80°	12.6	1.0
80°-90°	3.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	839.7	63.9
0°-40°	1107.3	84.2
0°-60°	1275.0	97.0
0°-90°	1315.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1315.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1520	
5°	1480	138
15°	1205	335
25°	804	367
35°	426	268
45°	159	126
55°	42	41
65°	24	23
75°	13	13
85°	4	4
90°	0	

TEST NUMBER: P1250508

CATALOG NUMBER: P3AS24R609027D010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1519.8
2.5°	1510.8
5°	1480.0
7.5°	1433.1
10°	1369.8
12.5°	1293.9
15°	1205.4
17.5°	1109.6
20°	1008.4
22.5°	905.4
25°	804.2
27.5°	703.0
30°	607.2
32.5°	515.0
35°	426.5
37.5°	347.0
40°	274.7
42.5°	211.4
45°	159.0
47.5°	115.7
50°	79.5
52.5°	52.4
55°	41.6
57.5°	36.1
60°	32.5
62.5°	27.1
65°	23.5
67.5°	19.9
70°	16.3
72.5°	14.5
75°	12.6
77.5°	9.0
80°	7.2
82.5°	5.4
85°	3.6
87.5°	1.8
90°	0.0

(END OF REPORT)