

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249451

Luminaire Tested: P3AS13R659027DE010 E3D1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249451
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659027DE010 E3D1MW
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 90CRI , E3D1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1122.0 lumens
Efficiency: N/A
Efficacy: 76.8 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249451

CATALOG NUMBER: P3AS13R659027DE010 E3D1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1249451

CATALOG NUMBER: P3AS13R659027DE010 E3D1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94		
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87		
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81		
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	75		
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70		
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66		
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62		
8	80	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58		
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54		
10	72	63	57	53	71	62	57	53	61	56	53	60	56	53	60	55	52	51		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	274189
5°	258067
10°	254772
15°	250285
20°	236317
25°	219327
30°	170482
35°	98618
40°	39732
45°	18296
50°	7130
55°	2791
60°	2368
65°	2335
70°	2308
75°	2288
80°	2273
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 18296 cd/sqm

TEST NUMBER: P1249451

CATALOG NUMBER: P3AS13R659027DE010 E3D1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.4	9.9
10°-20°	307.9	27.4
20°-30°	403.0	35.9
30°-40°	233.4	20.8
40°-50°	50.0	4.5
50°-60°	8.2	0.7
60°-70°	4.5	0.4
70°-80°	2.6	0.2
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	822.4	73.3
0°-40°	1055.8	94.1
0°-60°	1113.9	99.3
0°-90°	1122.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1122.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1250	
5°	1172	111
15°	1102	308
25°	906	403
35°	368	233
45°	59	50
55°	7	8
65°	4	4
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1249451

CATALOG NUMBER: P3AS13R659027DE010 E3D1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1250.4
2.5°	1215.0
5°	1172.4
7.5°	1155.1
10°	1144.2
12.5°	1128.8
15°	1102.5
17.5°	1061.7
20°	1012.7
22.5°	966.4
25°	906.5
27.5°	805.8
30°	673.3
32.5°	521.8
35°	368.4
37.5°	233.2
40°	138.8
42.5°	87.1
45°	59.0
47.5°	38.1
50°	20.9
52.5°	10.0
55°	7.3
57.5°	6.4
60°	5.4
62.5°	5.4
65°	4.5
67.5°	3.6
70°	3.6
72.5°	2.7
75°	2.7
77.5°	1.8
80°	1.8
82.5°	0.9
85°	0.9
87.5°	0.9
90°	0.0

(END OF REPORT)