

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250518

Luminaire Tested: P3AS24R659027D010 E3D1WH

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1250518  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-16)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS24R659027D010 E3D1WH  
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 90CRI , E3D1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2156.0 lumens  
Efficiency: N/A  
Efficacy: 74.9 lumens/watt  
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.88  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1250518  
CATALOG NUMBER: P3AS24R659027D010 E3D1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1250518  
 CATALOG NUMBER: P3AS24R659027D010 E3D1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			
3	103	97	92	88	101	95	91	88	93	89	86	90	87	85	88	86	83	82			
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	81	78	77			
5	93	85	79	75	92	84	79	75	82	78	74	81	77	74	79	76	73	72			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			
7	84	75	70	65	83	75	69	65	73	69	65	72	68	65	71	67	64	63			
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59			
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56			
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	577717
5°	536428
10°	518739
15°	499912
20°	462180
25°	421089
30°	325341
35°	188589
40°	74826
45°	31879
50°	7573
55°	1032
60°	789
65°	467
70°	577
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 31879 cd/sqm



TEST NUMBER: P1250518  
 CATALOG NUMBER: P3AS24R659027D010 E3D1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	229.8	10.7
10°-20°	613.6	28.5
20°-30°	776.6	36.0
30°-40°	442.2	20.5
40°-50°	87.9	4.1
50°-60°	4.6	0.2
60°-70°	1.2	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1620.0	75.1
0°-40°	2062.3	95.7
0°-60°	2154.7	99.9
0°-90°	2156.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2156.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2635	
5°	2437	230
15°	2202	614
25°	1740	777
35°	704	442
45°	103	88
55°	3	5
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1250518  
CATALOG NUMBER: P3AS24R659027D010 E3D1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2634.6
1°	2615.1
2°	2572.6
3°	2522.9
4°	2474.2
5°	2437.0
6°	2409.5
7°	2387.3
8°	2367.8
9°	2348.4
10°	2329.7
11°	2309.4
12°	2288.1
13°	2262.4
14°	2234.9
15°	2202.1
16°	2163.1
17°	2120.6
18°	2074.5
19°	2025.8
20°	1980.6
21°	1934.5
22°	1892.9
23°	1849.4
24°	1798.9
25°	1740.4
26°	1670.4
27°	1586.2
28°	1491.4
29°	1390.4
30°	1284.9
31°	1168.9
32°	1053.7
32.5°	994.3
33°	936.7
34°	819.7
35°	704.5
36°	598.2
37°	492.7
37.5°	438.7
38°	395.2
39°	319.9
40°	261.4
42.5°	161.3
45°	102.8



TEST NUMBER: P1250518  
CATALOG NUMBER: P3AS24R659027D010 E3D1WH

**CANDELA DISTRIBUTION (continued):**

	0°
47.5°	60.3
50°	22.2
52.5°	4.4
55°	2.7
57.5°	1.8
60°	1.8
62.5°	1.8
65°	0.9
67.5°	0.9
70°	0.9
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)