

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249456

Luminaire Tested: P3AS13R659027DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249456
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659027DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 90CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 910.0 lumens
Efficiency: N/A
Efficacy: 62.3 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249456

CATALOG NUMBER: P3AS13R659027DE010 E3DL1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1249456

CATALOG NUMBER: P3AS13R659027DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67
8	77	67	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	59	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	214610
5°	212040
10°	203982
15°	191079
20°	171865
25°	145944
30°	114144
35°	81352
40°	53214
45°	32903
50°	16716
55°	5887
60°	5175
65°	5189
70°	4680
75°	4575
80°	4546
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 32903 cd/sqm

TEST NUMBER: P1249456

CATALOG NUMBER: P3AS13R659027DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.4	9.9
10°-20°	234.3	25.7
20°-30°	273.8	30.1
30°-40°	191.3	21.0
40°-50°	84.2	9.3
50°-60°	18.7	2.1
60°-70°	9.6	1.1
70°-80°	5.7	0.6
80°-90°	2.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	598.5	65.8
0°-40°	789.8	86.8
0°-60°	892.8	98.1
0°-90°	910.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	910.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	979	
5°	963	90
15°	842	234
25°	603	274
35°	304	191
45°	106	84
55°	15	19
65°	10	10
75°	5	6
85°	2	2
90°	0	

TEST NUMBER: P1249456

CATALOG NUMBER: P3AS13R659027DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	978.7
2.5°	975.0
5°	963.3
7.5°	943.3
10°	916.1
12.5°	882.5
15°	841.7
17.5°	791.8
20°	736.5
22.5°	673.9
25°	603.2
27.5°	528.8
30°	450.8
32.5°	375.5
35°	303.9
37.5°	241.3
40°	185.9
42.5°	140.6
45°	106.1
47.5°	78.0
50°	49.0
52.5°	25.4
55°	15.4
57.5°	13.6
60°	11.8
62.5°	10.9
65°	10.0
67.5°	8.2
70°	7.3
72.5°	6.3
75°	5.4
77.5°	4.5
80°	3.6
82.5°	2.7
85°	1.8
87.5°	0.9
90°	0.0

(END OF REPORT)