

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250520

Luminaire Tested: P3AS24R659027D010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250520
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS24R659027D010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 889.0 lumens
Efficiency: N/A
Efficacy: 30.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250520

CATALOG NUMBER: P3AS24R659027D010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1250520

CATALOG NUMBER: P3AS24R659027D010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67
8	77	67	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	59	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	209654
5°	207131
10°	199262
15°	186675
20°	167898
25°	142557
30°	111511
35°	79451
40°	51983
45°	32158
50°	16307
55°	5773
60°	5043
65°	5033
70°	4552
75°	4490
80°	4420
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 32158 cd/sqm

TEST NUMBER: P1250520

CATALOG NUMBER: P3AS24R659027D010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.3	9.9
10°-20°	228.9	25.7
20°-30°	267.5	30.1
30°-40°	186.9	21.0
40°-50°	82.3	9.3
50°-60°	18.3	2.1
60°-70°	9.3	1.0
70°-80°	5.6	0.6
80°-90°	1.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	584.7	65.8
0°-40°	771.6	86.8
0°-60°	872.1	98.1
0°-90°	889.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	889.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	956	
5°	941	88
15°	822	229
25°	589	267
35°	297	187
45°	104	82
55°	15	18
65°	10	9
75°	5	6
85°	2	2
90°	0	

TEST NUMBER: P1250520

CATALOG NUMBER: P3AS24R659027D010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	956.1
2.5°	952.5
5°	941.0
7.5°	921.5
10°	894.9
12.5°	862.2
15°	822.3
17.5°	773.6
20°	719.5
22.5°	658.4
25°	589.2
27.5°	516.6
30°	440.4
32.5°	366.8
35°	296.8
37.5°	235.7
40°	181.6
42.5°	137.3
45°	103.7
47.5°	76.2
50°	47.8
52.5°	24.8
55°	15.1
57.5°	13.3
60°	11.5
62.5°	10.6
65°	9.7
67.5°	8.0
70°	7.1
72.5°	6.2
75°	5.3
77.5°	4.4
80°	3.5
82.5°	2.7
85°	1.8
87.5°	0.9
90°	0.0

(END OF REPORT)