

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249519

Luminaire Tested: P3AS17R129027DE010 E3DLD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249519
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R129027DE010 E3DLD1MW
Description: 3in Adjustable LED luminaire with, R12 optic, 2700K CCT AND, 90CRI , E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 801.0 lumens
Efficiency: N/A
Efficacy: 35.0 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 22.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249519

CATALOG NUMBER: P3AS17R129027DE010 E3DLD1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1249519

CATALOG NUMBER: P3AS17R129027DE010 E3DLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83		
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76		
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70		
5	89	80	73	68	87	79	73	68	77	72	67	75	71	67	74	69	66	65		
6	84	74	68	63	83	73	67	63	72	66	62	70	66	62	69	65	61	60		
7	80	69	63	58	78	69	63	58	67	62	58	66	61	57	65	61	57	56		
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52		
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49		
10	68	58	52	48	67	57	51	47	57	51	47	56	51	47	55	50	47	46		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	202045
5°	196566
10°	179623
15°	157345
20°	134972
25°	112700
30°	90191
35°	67646
40°	49092
45°	32096
50°	20093
55°	13572
60°	12017
65°	11052
70°	10386
75°	9489
80°	8966
85°	7548

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 32096 cd/sqm

TEST NUMBER: P1249519

CATALOG NUMBER: P3AS17R129027DE010 E3DLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.4	10.3
10°-20°	193.1	24.1
20°-30°	212.8	26.6
30°-40°	159.4	19.9
40°-50°	82.6	10.3
50°-60°	34.2	4.3
60°-70°	21.2	2.6
70°-80°	11.9	1.5
80°-90°	3.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	488.3	61.0
0°-40°	647.6	80.9
0°-60°	764.5	95.4
0°-90°	801.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	801.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	921	
5°	893	82
15°	693	193
25°	466	213
35°	253	159
45°	104	83
55°	36	34
65°	21	21
75°	11	12
85°	3	3
90°	0	

TEST NUMBER: P1249519

CATALOG NUMBER: P3AS17R129027DE010 E3DLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	921.4
1°	922.4
2°	919.4
3°	913.3
4°	904.1
5°	893.0
6°	878.8
7°	863.5
8°	845.3
9°	826.0
10°	806.7
12.5°	750.9
15°	693.1
17.5°	635.2
20°	578.4
22.5°	520.6
25°	465.8
27.5°	411.0
30°	356.2
32.5°	302.4
35°	252.7
37.5°	210.1
40°	171.5
42.5°	136.0
45°	103.5
47.5°	78.1
50°	58.9
52.5°	43.6
55°	35.5
57.5°	31.5
60°	27.4
62.5°	24.4
65°	21.3
67.5°	18.3
70°	16.2
72.5°	13.2
75°	11.2
77.5°	9.1
80°	7.1
82.5°	5.1
85°	3.0
87.5°	1.0
90°	0.0

(END OF REPORT)