

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250662

Luminaire Tested: P3AS02R129030DE010 E3DLP1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250662
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R129030DE010 E3DLP1H
Description: 3in Adjustable LED luminaire with, R12 optic, 3000K CCT AND, 90CRI , E3DLP1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 147.0 lumens
Efficiency: N/A
Efficacy: 39.7 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250662

CATALOG NUMBER: P3AS02R129030DE010 E3DLP1H

Luminous Intensity Polar Plot



TEST NUMBER: P1250662

CATALOG NUMBER: P3AS02R129030DE010 E3DLP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	108	106		111	108	106	104		104	102	101		100	99	98		97	96	95
2	108	103	98	95		105	101	97	94		98	95	92		95	92	90		92	90	88
3	102	96	91	87		100	94	90	86		92	88	85		89	86	83		87	84	82
4	97	90	84	80		95	88	83	79		86	82	78		84	81	78		82	79	77
5	93	84	78	74		91	83	78	74		81	77	73		80	76	72		78	75	72
6	88	79	73	69		87	79	73	69		77	72	69		76	71	68		74	71	68
7	84	75	69	65		83	74	69	65		73	68	64		72	67	64		71	67	64
8	80	71	65	61		79	71	65	61		69	64	61		68	64	61		67	63	60
9	77	68	62	58		76	67	62	58		66	61	58		65	61	57		64	60	57
10	74	64	59	55		73	64	59	55		63	58	55		62	58	55		62	57	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	63394
5°	58595
10°	46782
15°	35324
20°	26906
25°	20493
30°	14686
35°	9583
40°	5868
45°	3566
50°	2354
55°	1835
60°	1579
65°	1349
70°	1218
75°	1186
80°	884
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3566 cd/sqm

TEST NUMBER: P1250662

CATALOG NUMBER: P3AS02R129030DE010 E3DLP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	23.6	16.0
10°-20°	43.5	29.6
20°-30°	38.7	26.3
30°-40°	22.9	15.6
40°-50°	9.4	6.4
50°-60°	4.4	3.0
60°-70°	2.7	1.8
70°-80°	1.4	1.0
80°-90°	0.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	105.8	72.0
0°-40°	128.7	87.6
0°-60°	142.6	97.0
0°-90°	147.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	147.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	289	
5°	266	24
15°	156	44
25°	85	39
35°	36	23
45°	12	9
55°	5	4
65°	3	3
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1250662

CATALOG NUMBER: P3AS02R129030DE010 E3DLP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	289.1
1°	288.4
2°	286.2
3°	281.9
4°	274.8
5°	266.2
6°	256.9
7°	245.9
8°	234.4
9°	222.7
10°	210.1
12.5°	181.2
15°	155.6
17.5°	133.7
20°	115.3
22.5°	99.1
25°	84.7
27.5°	70.9
30°	58.0
32.5°	46.3
35°	35.8
37.5°	27.5
40°	20.5
42.5°	15.3
45°	11.5
47.5°	8.8
50°	6.9
52.5°	5.7
55°	4.8
57.5°	4.1
60°	3.6
62.5°	3.1
65°	2.6
67.5°	2.4
70°	1.9
72.5°	1.7
75°	1.4
77.5°	1.0
80°	0.7
82.5°	0.5
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)