

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250685

Luminaire Tested: P3AS02R159030DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250685
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R159030DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 90CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 253.0 lumens
Efficiency: N/A
Efficacy: 70.3 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250685

CATALOG NUMBER: P3AS02R159030DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1250685

CATALOG NUMBER: P3AS02R159030DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	103	100	108	104	101	99	101	99	97		98	96	95		96
3	106	101	97	93	104	99	96	93	97	94	91		94	92	90		92
4	102	96	92	88	100	95	91	88	93	89	87		91	88	86		89
5	98	92	87	84	97	91	87	83	89	86	83		88	84	82		86
6	95	88	83	80	94	87	83	80	86	82	79		85	81	79		83
7	92	85	80	77	91	84	80	76	83	79	76		82	78	76		81
8	89	81	77	74	88	81	77	73	80	76	73		79	76	73		78
9	86	79	74	71	85	78	74	71	77	73	71		77	73	70		76
10	84	76	71	68	83	76	71	68	75	71	68		74	71	68		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	216123
5°	191855
10°	133220
15°	78797
20°	44874
25°	25647
30°	14205
35°	7576
40°	4179
45°	2264
50°	1399
55°	1109
60°	965
65°	882
70°	769
75°	847
80°	631
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2264 cd/sqm

TEST NUMBER: P1250685

CATALOG NUMBER: P3AS02R159030DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.1	29.3
10°-20°	97.8	38.7
20°-30°	50.4	19.9
30°-40°	18.9	7.5
40°-50°	6.2	2.4
50°-60°	2.6	1.0
60°-70°	1.7	0.7
70°-80°	1.0	0.4
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	222.3	87.9
0°-40°	241.2	95.4
0°-60°	250.0	98.8
0°-90°	253.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	253.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	986	
5°	872	74
15°	347	98
25°	106	50
35°	28	19
45°	7	6
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1250685

CATALOG NUMBER: P3AS02R159030DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	985.6
1°	983.7
2°	970.8
3°	946.1
4°	913.7
5°	871.6
6°	823.8
7°	771.4
8°	713.1
9°	655.6
10°	598.3
12.5°	460.4
15°	347.1
17.5°	259.8
20°	192.3
22.5°	143.6
25°	106.0
27.5°	77.3
30°	56.1
32.5°	39.7
35°	28.3
37.5°	20.2
40°	14.6
42.5°	10.5
45°	7.3
47.5°	5.4
50°	4.1
52.5°	3.4
55°	2.9
57.5°	2.4
60°	2.2
62.5°	1.9
65°	1.7
67.5°	1.5
70°	1.2
72.5°	1.2
75°	1.0
77.5°	0.7
80°	0.5
82.5°	0.5
85°	0.2
87.5°	0.0
90°	0.0

(END OF REPORT)