

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250744

Luminaire Tested: P3AS02R259030DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250744
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R259030DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 96.0 lumens
Efficiency: N/A
Efficacy: 26.7 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250744

CATALOG NUMBER: P3AS02R259030DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1250744

CATALOG NUMBER: P3AS02R259030DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	22805
5°	22276
10°	20641
15°	18388
20°	15798
25°	13428
30°	11065
35°	8620
40°	6183
45°	3938
50°	2320
55°	1606
60°	1447
65°	1349
70°	1218
75°	1101
80°	1010
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3938 cd/sqm

TEST NUMBER: P1250744

CATALOG NUMBER: P3AS02R259030DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	9.4	9.8
10°-20°	22.5	23.4
20°-30°	25.4	26.5
30°-40°	20.1	20.9
40°-50°	10.1	10.6
50°-60°	4.0	4.2
60°-70°	2.6	2.7
70°-80°	1.4	1.5
80°-90°	0.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	57.3	59.7
0°-40°	77.4	80.6
0°-60°	91.5	95.4
0°-90°	96.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	96.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	104	
5°	101	9
15°	81	22
25°	56	25
35°	32	20
45°	13	10
55°	4	4
65°	3	3
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1250744

CATALOG NUMBER: P3AS02R259030DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	104.0
1°	104.0
2°	103.7
3°	103.1
4°	102.3
5°	101.2
6°	99.9
7°	98.3
8°	96.6
9°	94.7
10°	92.7
11°	90.4
12°	88.3
13°	85.8
14°	83.4
15°	81.0
17.5°	74.3
20°	67.7
22.5°	61.5
25°	55.5
27.5°	49.6
30°	43.7
32.5°	38.0
35°	32.2
37.5°	26.8
40°	21.6
42.5°	16.9
45°	12.7
47.5°	9.4
50°	6.8
52.5°	5.1
55°	4.2
57.5°	3.8
60°	3.3
62.5°	3.0
65°	2.6
67.5°	2.3
70°	1.9
72.5°	1.7
75°	1.3
77.5°	1.1
80°	0.8
82.5°	0.6
85°	0.4
87.5°	0.1



TEST NUMBER: P1250744

CATALOG NUMBER: P3AS02R259030DE010 E3DLD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)