

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250747

Luminaire Tested: P3AS02R259030DE010 E3DLD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250747
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R259030DE010 E3DLD1MW
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 90CRI , E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 195.9 lumens
Efficiency: N/A
Efficacy: 54.4 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250747
CATALOG NUMBER: P3AS02R259030DE010 E3DLD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1250747
 CATALOG NUMBER: P3AS02R259030DE010 E3DLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83			
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	83	80	78	76			
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70			
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64			
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59			
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55			
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51			
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48			
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	46575
5°	45476
10°	42128
15°	37526
20°	32249
25°	27413
30°	22560
35°	17587
40°	12652
45°	8032
50°	4742
55°	3250
60°	2982
65°	2802
70°	2500
75°	2288
80°	2147
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8032 cd/sqm



TEST NUMBER: P1250747
 CATALOG NUMBER: P3AS02R259030DE010 E3DLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.2	9.8
10°-20°	45.9	23.4
20°-30°	51.8	26.5
30°-40°	41.0	20.9
40°-50°	20.7	10.6
50°-60°	8.3	4.2
60°-70°	5.3	2.7
70°-80°	2.9	1.5
80°-90°	0.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	116.9	59.7
0°-40°	157.9	80.6
0°-60°	186.9	95.4
0°-90°	195.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	195.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	212	
5°	207	19
15°	165	46
25°	113	52
35°	66	41
45°	26	21
55°	8	8
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1250747
CATALOG NUMBER: P3AS02R259030DE010 E3DLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	212.4
1°	212.4
2°	211.7
3°	210.5
4°	208.8
5°	206.6
6°	203.9
7°	200.7
8°	197.3
9°	193.4
10°	189.2
11°	184.6
12°	180.2
13°	175.1
14°	170.2
15°	165.3
17.5°	151.6
20°	138.2
22.5°	125.5
25°	113.3
27.5°	101.3
30°	89.1
32.5°	77.6
35°	65.7
37.5°	54.7
40°	44.2
42.5°	34.4
45°	25.9
47.5°	19.3
50°	13.9
52.5°	10.5
55°	8.5
57.5°	7.8
60°	6.8
62.5°	6.1
65°	5.4
67.5°	4.6
70°	3.9
72.5°	3.4
75°	2.7
77.5°	2.2
80°	1.7
82.5°	1.2
85°	0.7
87.5°	0.2



TEST NUMBER: P1250747
CATALOG NUMBER: P3AS02R259030DE010 E3DLD1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)