

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250769

Luminaire Tested: P3AS02R309030DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250769
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R309030DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 308.0 lumens
Efficiency: N/A
Efficacy: 85.5 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250769
CATALOG NUMBER: P3AS02R309030DE010 E3D1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1250769
 CATALOG NUMBER: P3AS02R309030DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	96	95	97
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	94	93	92	94
3	108	103	100	97	106	102	99	96	99	97	95	97	95	93	95	93	92	91	90	89	91
4	105	99	95	92	103	98	95	92	96	93	91	94	92	90	93	91	89	88	87	86	88
5	101	96	92	89	100	95	91	88	93	90	87	92	89	87	90	88	86	85	84	83	85
6	99	92	88	85	97	92	88	85	90	87	85	89	86	84	88	85	83	82	81	80	82
7	96	89	85	82	95	89	85	82	88	84	82	87	84	81	86	83	81	80	79	78	80
8	93	87	83	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	77	76	78
9	91	84	80	77	90	84	80	77	83	79	77	82	79	77	82	79	77	76	75	74	76
10	88	82	78	75	88	81	78	75	81	77	75	80	77	75	80	77	75	74	73	72	74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	245046
5°	241866
10°	211174
15°	134212
20°	53181
25°	17759
30°	8254
35°	3748
40°	1431
45°	713
50°	205
55°	76
60°	44
65°	52
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 713 cd/sqm



TEST NUMBER: P1250769

CATALOG NUMBER: P3AS02R309030DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.5	32.6
10°-20°	155.8	50.6
20°-30°	40.2	13.0
30°-40°	9.4	3.1
40°-50°	1.8	0.6
50°-60°	0.2	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	296.4	96.3
0°-40°	305.8	99.3
0°-60°	307.9	100.0
0°-90°	308.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	308.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1118	
5°	1099	100
15°	591	156
25°	73	40
35°	14	9
45°	2	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1250769
CATALOG NUMBER: P3AS02R309030DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1117.5
1°	1116.7
2°	1114.1
3°	1111.1
4°	1106.7
5°	1098.8
6°	1086.0
7°	1064.7
8°	1035.6
9°	997.7
10°	948.4
11°	889.7
12°	825.6
13°	751.8
14°	674.6
15°	591.2
16°	509.6
17°	430.9
18°	355.5
19°	286.2
20°	227.9
21°	179.3
22°	141.1
23°	111.7
24°	89.4
25°	73.4
26°	61.2
27°	52.0
28°	45.0
29°	38.5
30°	32.6
32.5°	20.6
35°	14.0
37.5°	8.7
40°	5.0
42.5°	3.3
45°	2.3
47.5°	1.3
50°	0.6
52.5°	0.2
55°	0.2
57.5°	0.1
60°	0.1
62.5°	0.1
65°	0.1



TEST NUMBER: P1250769
CATALOG NUMBER: P3AS02R309030DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)