

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250775

Luminaire Tested: P3AS02R309030DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250775
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R309030DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 90CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 257.9 lumens
Efficiency: N/A
Efficacy: 71.6 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250775

CATALOG NUMBER: P3AS02R309030DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1250775

CATALOG NUMBER: P3AS02R309030DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	105	102	99	108	104	101	98	101	98	96		98	96	94		95
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91
4	101	95	90	87	99	94	89	86	92	88	85		90	87	84		88
5	97	90	85	82	96	89	85	81	88	84	81		86	83	80		85
6	94	86	81	78	92	85	81	77	84	80	77		83	79	76		81
7	90	82	77	74	89	82	77	74	81	76	73		80	76	73		79
8	87	79	74	71	86	79	74	71	78	73	70		77	73	70		76
9	84	76	71	68	83	75	71	68	75	70	67		74	70	67		73
10	81	73	68	65	80	73	68	65	72	68	65		71	67	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	150558
5°	143297
10°	120528
15°	86924
20°	53905
25°	30655
30°	17041
35°	9262
40°	4895
45°	2636
50°	1399
55°	918
60°	833
65°	882
70°	769
75°	593
80°	631
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2636 cd/sqm

TEST NUMBER: P1250775

CATALOG NUMBER: P3AS02R309030DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.6	22.7
10°-20°	104.2	40.4
20°-30°	60.2	23.3
30°-40°	22.9	8.9
40°-50°	7.0	2.7
50°-60°	2.3	0.9
60°-70°	1.6	0.6
70°-80°	0.9	0.3
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	223.0	86.5
0°-40°	245.9	95.3
0°-60°	255.2	98.9
0°-90°	257.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	257.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	687	
5°	651	59
15°	383	104
25°	127	60
35°	35	23
45°	8	7
55°	2	2
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1250775

CATALOG NUMBER: P3AS02R309030DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	686.6
1°	686.1
2°	681.9
3°	674.1
4°	664.4
5°	651.0
6°	633.9
7°	614.9
8°	593.7
9°	568.4
10°	541.3
11°	512.1
12°	481.1
13°	448.7
14°	415.8
15°	382.9
17.5°	302.0
20°	231.0
22.5°	171.3
25°	126.7
27.5°	92.1
30°	67.3
32.5°	48.5
35°	34.6
37.5°	24.1
40°	17.1
42.5°	11.9
45°	8.5
47.5°	5.8
50°	4.1
52.5°	2.9
55°	2.4
57.5°	2.2
60°	1.9
62.5°	1.7
65°	1.7
67.5°	1.5
70°	1.2
72.5°	1.0
75°	0.7
77.5°	0.7
80°	0.5
82.5°	0.5
85°	0.2
87.5°	0.0



TEST NUMBER: P1250775
CATALOG NUMBER: P3AS02R309030DE010 E3DL1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)