

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250782

Luminaire Tested: P3AS02R309030DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250782
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R309030DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 77.0 lumens
Efficiency: N/A
Efficacy: 21.4 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250782
CATALOG NUMBER: P3AS02R309030DE010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1250782
 CATALOG NUMBER: P3AS02R309030DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	95	90	86	100	94	89	85	91	87	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74	74	74	74
5	92	84	78	73	90	83	77	73	81	76	72	79	75	72	78	74	71	70	70	70	70
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65	65	65	65
7	83	74	68	64	82	74	68	64	72	67	63	71	67	63	70	66	63	61	61	61	61
8	80	70	64	60	78	70	64	60	69	63	60	68	63	60	67	62	59	58	58	58	58
9	76	67	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55	55	55	55
10	73	63	58	54	72	63	57	54	62	57	54	61	57	53	61	56	53	52	52	52	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	26314
5°	25490
10°	22979
15°	19001
20°	14701
25°	11033
30°	8001
35°	5327
40°	3292
45°	1923
50°	1194
55°	956
60°	833
65°	675
70°	641
75°	593
80°	505
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1923 cd/sqm



TEST NUMBER: P1250782
 CATALOG NUMBER: P3AS02R309030DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	10.7	13.8
10°-20°	23.1	29.9
20°-30°	21.0	27.2
30°-40°	12.7	16.5
40°-50°	5.1	6.6
50°-60°	2.2	2.9
60°-70°	1.4	1.8
70°-80°	0.7	1.0
80°-90°	0.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
<hr/>		
0°-30°	54.7	71.0
0°-40°	67.4	87.5
0°-60°	74.7	97.0
0°-90°	77.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	77.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	120	
5°	116	11
15°	84	23
25°	46	21
35°	20	13
45°	6	5
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1250782
CATALOG NUMBER: P3AS02R309030DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	120.0
1°	119.9
2°	119.4
3°	118.6
4°	117.4
5°	115.8
6°	113.9
7°	111.9
8°	109.2
9°	106.3
10°	103.2
11°	99.6
12°	95.8
13°	91.9
14°	87.8
15°	83.7
17.5°	73.1
20°	63.0
22.5°	53.7
25°	45.6
27.5°	38.2
30°	31.6
32.5°	25.6
35°	19.9
37.5°	15.3
40°	11.5
42.5°	8.4
45°	6.2
47.5°	4.7
50°	3.5
52.5°	2.7
55°	2.5
57.5°	2.1
60°	1.9
62.5°	1.6
65°	1.3
67.5°	1.2
70°	1.0
72.5°	0.8
75°	0.7
77.5°	0.6
80°	0.4
82.5°	0.2
85°	0.2
87.5°	0.1



TEST NUMBER: P1250782
CATALOG NUMBER: P3AS02R309030DE010 E3DLP1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)