

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250792

Luminaire Tested: P3AS02R359030DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250792
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R359030DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 309.0 lumens
Efficiency: N/A
Efficacy: 85.8 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250792
CATALOG NUMBER: P3AS02R359030DE010 E3CB1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1250792
 CATALOG NUMBER: P3AS02R359030DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	115	113	111	109	112	110	109	107	107	105	104	103	102	101	99	99	98	96			96
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	93			93
3	107	102	98	95	105	101	98	95	98	96	93	96	94	92	94	92	90	89			89
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86			86
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	83			83
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	80			80
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	78			78
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	75			75
9	89	82	77	74	88	81	77	74	80	77	74	80	76	74	79	76	74	73			73
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	71	70			70

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	201497
5°	197380
10°	183631
15°	134621
20°	68933
25°	24848
30°	9672
35°	3400
40°	1403
45°	372
50°	341
55°	382
60°	307
65°	259
70°	321
75°	424
80°	253
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 424 cd/sqm



TEST NUMBER: P1250792
 CATALOG NUMBER: P3AS02R359030DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.6	27.1
10°-20°	156.8	50.8
20°-30°	55.5	18.0
30°-40°	9.7	3.1
40°-50°	1.4	0.5
50°-60°	0.8	0.3
60°-70°	0.6	0.2
70°-80°	0.4	0.1
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	296.0	95.8
0°-40°	305.7	98.9
0°-60°	307.9	99.7
0°-90°	309.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	309.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	919	
5°	897	84
15°	593	157
25°	103	56
35°	13	10
45°	1	1
55°	1	1
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1250792
CATALOG NUMBER: P3AS02R359030DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	918.9
1°	918.6
2°	915.7
3°	910.1
4°	905.0
5°	896.7
6°	888.2
7°	878.7
8°	867.0
9°	848.8
10°	824.7
11°	791.3
12°	751.2
13°	703.5
14°	650.9
15°	593.0
17.5°	441.7
20°	295.4
22.5°	178.1
25°	102.7
27.5°	61.3
30°	38.2
32.5°	22.1
35°	12.7
37.5°	8.0
40°	4.9
42.5°	2.4
45°	1.2
47.5°	1.0
50°	1.0
52.5°	1.0
55°	1.0
57.5°	0.7
60°	0.7
62.5°	0.7
65°	0.5
67.5°	0.5
70°	0.5
72.5°	0.5
75°	0.5
77.5°	0.2
80°	0.2
82.5°	0.2
85°	0.0
87.5°	0.0



TEST NUMBER: P1250792
CATALOG NUMBER: P3AS02R359030DE010 E3CB1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)