

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249703

Luminaire Tested: P3AS17R409027DE010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249703
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R409027DE010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R40 optic, 2700K CCT AND, 90CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 882.9 lumens
Efficiency: N/A
Efficacy: 41.6 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249703

CATALOG NUMBER: P3AS17R409027DE010 E3DLP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1249703

CATALOG NUMBER: P3AS17R409027DE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	95	105	101	97	93	97	94	91		94	92	89		92
3	102	95	90	86	100	94	89	85	91	87	84		89	85	83		86
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	78	72	68	76	71	67		75	70	67		73
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	274956
5°	269381
10°	250808
15°	218594
20°	176182
25°	132056
30°	92850
35°	60820
40°	36812
45°	21987
50°	13134
55°	10552
60°	9473
65°	8094
70°	7694
75°	6100
80°	6061
85°	6038

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21987 cd/sqm

TEST NUMBER: P1249703

CATALOG NUMBER: P3AS17R409027DE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	113.6	12.9
10°-20°	265.2	30.0
20°-30°	249.9	28.3
30°-40°	144.5	16.4
40°-50°	57.6	6.5
50°-60°	25.5	2.9
60°-70°	15.7	1.8
70°-80°	8.2	0.9
80°-90°	2.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	628.8	71.2
0°-40°	773.3	87.6
0°-60°	856.4	97.0
0°-90°	882.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	882.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1254	
5°	1224	114
15°	963	265
25°	546	250
35°	227	145
45°	71	58
55°	28	25
65°	16	16
75°	7	8
85°	2	3
90°	0	

TEST NUMBER: P1249703

CATALOG NUMBER: P3AS17R409027DE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1253.9
2.5°	1246.6
5°	1223.8
7.5°	1181.7
10°	1126.4
12.5°	1051.9
15°	962.9
17.5°	863.2
20°	755.0
22.5°	646.8
25°	545.8
27.5°	452.0
30°	366.7
32.5°	292.1
35°	227.2
37.5°	171.9
40°	128.6
42.5°	96.2
45°	70.9
47.5°	51.7
50°	38.5
52.5°	31.3
55°	27.6
57.5°	25.2
60°	21.6
62.5°	18.0
65°	15.6
67.5°	13.2
70°	12.0
72.5°	9.6
75°	7.2
77.5°	6.0
80°	4.8
82.5°	3.6
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)