

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250815

Luminaire Tested: P3AS02R359030DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250815
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R359030DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 90CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 158.0 lumens
Efficiency: N/A
Efficacy: 43.9 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250815

CATALOG NUMBER: P3AS02R359030DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1250815

CATALOG NUMBER: P3AS02R359030DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	97	93	97	94	91		94	92	89		91
3	102	95	90	86	100	94	89	85	91	87	84		89	85	82		86
4	97	89	83	79	95	88	82	78	86	81	77		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	77	72	68	76	71	67		75	70	67		73
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	70	64	60	78	69	63	59	68	63	59		67	62	59		66
9	76	66	60	56	75	66	60	56	65	59	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	50785
5°	49527
10°	45290
15°	38434
20°	30429
25°	23009
30°	16762
35°	11323
40°	6956
45°	4000
50°	2422
55°	1950
60°	1710
65°	1505
70°	1218
75°	1271
80°	1263
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4000 cd/sqm

TEST NUMBER: P1250815

CATALOG NUMBER: P3AS02R359030DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	20.8	13.2
10°-20°	46.7	29.6
20°-30°	43.7	27.6
30°-40°	26.7	16.9
40°-50°	10.5	6.7
50°-60°	4.6	2.9
60°-70°	2.9	1.8
70°-80°	1.5	1.0
80°-90°	0.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	111.1	70.4
0°-40°	137.9	87.3
0°-60°	153.0	96.9
0°-90°	158.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	158.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	232	
5°	225	21
15°	169	47
25°	95	44
35°	42	27
45°	13	11
55°	5	5
65°	3	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1250815

CATALOG NUMBER: P3AS02R359030DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	231.6
1°	231.8
2°	231.1
3°	229.7
4°	227.5
5°	225.0
6°	221.9
7°	218.2
8°	213.8
9°	209.0
10°	203.4
11°	197.5
12°	191.2
13°	184.4
14°	176.9
15°	169.3
17.5°	149.9
20°	130.4
22.5°	111.7
25°	95.1
27.5°	79.8
30°	66.2
32.5°	53.5
35°	42.3
37.5°	32.4
40°	24.3
42.5°	17.5
45°	12.9
47.5°	9.2
50°	7.1
52.5°	5.8
55°	5.1
57.5°	4.4
60°	3.9
62.5°	3.4
65°	2.9
67.5°	2.4
70°	1.9
72.5°	1.7
75°	1.5
77.5°	1.2
80°	1.0
82.5°	0.7
85°	0.5
87.5°	0.2



TEST NUMBER: P1250815

CATALOG NUMBER: P3AS02R359030DE010 E3DLP1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)