

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249754

Luminaire Tested: P3AS17R509027DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249754
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R509027DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1053.0 lumens
Efficiency: N/A
Efficacy: 49.7 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249754

CATALOG NUMBER: P3AS17R509027DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1249754

CATALOG NUMBER: P3AS17R509027DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		95
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83
4	93	85	78	73	91	83	77	73	81	76	72		79	75	71		77
5	88	78	72	67	86	77	71	66	75	70	66		74	69	65		72
6	83	73	66	61	81	72	65	61	70	65	60		69	64	60		67
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	57	52	73	63	56	52	61	56	52		60	55	51		59
9	70	59	53	48	69	59	52	48	58	52	48		57	52	48		56
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	213996
5°	210829
10°	201510
15°	186607
20°	167711
25°	147420
30°	125361
35°	101670
40°	76372
45°	49183
50°	23368
55°	18389
60°	17411
65°	16189
70°	14618
75°	13217
80°	12123
85°	12077

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 49183 cd/sqm

TEST NUMBER: P1249754

CATALOG NUMBER: P3AS17R509027DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.8	8.5
10°-20°	229.2	21.8
20°-30°	278.5	26.4
30°-40°	236.2	22.4
40°-50°	122.7	11.6
50°-60°	44.3	4.2
60°-70°	30.6	2.9
70°-80°	16.6	1.6
80°-90°	5.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	597.4	56.7
0°-40°	833.6	79.2
0°-60°	1000.5	95.0
0°-90°	1053.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1053.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	976	
5°	958	90
15°	822	229
25°	609	278
35°	380	236
45°	159	123
55°	48	44
65°	31	31
75°	16	17
85°	5	5
90°	0	

TEST NUMBER: P1249754

CATALOG NUMBER: P3AS17R509027DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	975.9
2.5°	972.3
5°	957.8
7.5°	936.2
10°	905.0
12.5°	865.3
15°	822.0
17.5°	772.8
20°	718.7
22.5°	663.4
25°	609.3
27.5°	552.8
30°	495.1
32.5°	437.5
35°	379.8
37.5°	323.3
40°	266.8
42.5°	212.7
45°	158.6
47.5°	105.8
50°	68.5
52.5°	52.9
55°	48.1
57.5°	43.3
60°	39.7
62.5°	34.9
65°	31.2
67.5°	26.4
70°	22.8
72.5°	19.2
75°	15.6
77.5°	12.0
80°	9.6
82.5°	7.2
85°	4.8
87.5°	2.4
90°	0.0

(END OF REPORT)