

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250838

Luminaire Tested: P3AS02R409030DE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250838
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R409030DE010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 90CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 218.0 lumens
Efficiency: N/A
Efficacy: 60.6 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250838
CATALOG NUMBER: P3AS02R409030DE010 E3DLD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1250838
 CATALOG NUMBER: P3AS02R409030DE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			55
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	48943
5°	48052
10°	45290
15°	41135
20°	36146
25°	30873
30°	25574
35°	19729
40°	14026
45°	9458
50°	5151
55°	3632
60°	3421
65°	3165
70°	2821
75°	2711
80°	2147
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9458 cd/sqm



TEST NUMBER: P1250838
 CATALOG NUMBER: P3AS02R409030DE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	20.4	9.3
10°-20°	50.5	23.2
20°-30°	58.4	26.8
30°-40°	46.0	21.1
40°-50°	23.6	10.8
50°-60°	9.0	4.1
60°-70°	6.0	2.7
70°-80°	3.3	1.5
80°-90°	1.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	129.2	59.3
0°-40°	175.2	80.4
0°-60°	207.8	95.3
0°-90°	218.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	218.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	223	
5°	218	20
15°	181	50
25°	128	58
35°	74	46
45°	30	24
55°	10	9
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1250838
CATALOG NUMBER: P3AS02R409030DE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	223.2
2.5°	221.9
5°	218.3
7.5°	211.9
10°	203.4
12.5°	193.4
15°	181.2
17.5°	168.5
20°	154.9
22.5°	141.0
25°	127.6
27.5°	114.1
30°	101.0
32.5°	87.6
35°	73.7
37.5°	60.7
40°	49.0
42.5°	39.0
45°	30.5
47.5°	22.2
50°	15.1
52.5°	11.0
55°	9.5
57.5°	8.5
60°	7.8
62.5°	6.8
65°	6.1
67.5°	5.1
70°	4.4
72.5°	3.7
75°	3.2
77.5°	2.4
80°	1.7
82.5°	1.5
85°	0.7
87.5°	0.5
90°	0.0

(END OF REPORT)