

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249764

Luminaire Tested: P3AS17R559027DE010 E3CD1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249764
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-36)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R559027DE010 E3CD1MB
Description: 3in Adjustable LED luminaire with, R55 optic, 2700K CCT AND, 90CRI , E3CD1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1600.0 lumens
Efficiency: N/A
Efficacy: 75.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249764

CATALOG NUMBER: P3AS17R559027DE010 E3CD1MB

Luminous Intensity Polar Plot



TEST NUMBER: P1249764

CATALOG NUMBER: P3AS17R559027DE010 E3CD1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94		
2	109	104	101	98	107	103	99	96	100	97	94	97	94	92	94	92	90	89		
3	104	98	94	90	102	97	93	89	94	91	88	92	89	86	90	87	85	84		
4	99	92	87	84	98	91	87	83	89	85	82	87	84	81	86	83	80	79		
5	95	87	82	78	93	86	81	78	85	80	77	83	79	76	82	78	76	74		
6	91	83	77	73	89	82	77	73	80	76	72	79	75	72	78	74	72	70		
7	87	78	73	69	85	78	72	69	76	72	68	75	71	68	74	70	68	66		
8	83	74	69	65	82	74	69	65	73	68	65	72	67	64	71	67	64	63		
9	79	71	65	61	78	70	65	61	69	64	61	68	64	61	68	64	61	60		
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	443758
5°	439642
10°	457306
15°	450967
20°	415836
25°	338366
30°	205525
35°	71126
40°	20295
45°	9706
50°	4094
55°	1835
60°	2105
65°	1868
70°	1539
75°	2033
80°	1515
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9706 cd/sqm

TEST NUMBER: P1249764

CATALOG NUMBER: P3AS17R559027DE010 E3CD1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	193.1	12.1
10°-20°	552.1	34.5
20°-30°	615.5	38.5
30°-40°	201.3	12.6
40°-50°	26.5	1.7
50°-60°	5.6	0.3
60°-70°	3.3	0.2
70°-80°	2.1	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1360.7	85.0
0°-40°	1562.0	97.6
0°-60°	1594.2	99.6
0°-90°	1600.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1600.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2024	
5°	1997	193
15°	1986	552
25°	1398	615
35°	266	201
45°	31	27
55°	5	6
65°	4	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1249764

CATALOG NUMBER: P3AS17R559027DE010 E3CD1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	2023.7
2.5°	2009.3
5°	1997.3
7.5°	2026.1
10°	2053.8
12.5°	2039.4
15°	1986.5
17.5°	1902.3
20°	1782.0
22.5°	1616.1
25°	1398.5
27.5°	1121.9
30°	811.7
32.5°	497.8
35°	265.7
37.5°	134.7
40°	70.9
42.5°	45.7
45°	31.3
47.5°	21.6
50°	12.0
52.5°	7.2
55°	4.8
57.5°	4.8
60°	4.8
62.5°	3.6
65°	3.6
67.5°	2.4
70°	2.4
72.5°	2.4
75°	2.4
77.5°	1.2
80°	1.2
82.5°	1.2
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)