

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250866

Luminaire Tested: P3AS02R459030DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250866
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-26)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R459030DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 211.0 lumens
Efficiency: N/A
Efficacy: 58.6 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.92
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250866

CATALOG NUMBER: P3AS02R459030DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1250866

CATALOG NUMBER: P3AS02R459030DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	82	97	91	85	81	88	83	80		85	81	78		83
4	94	85	78	74	92	84	78	73	81	76	72		79	75	71		77
5	88	79	72	67	86	78	71	67	76	70	66		74	69	65		72
6	83	73	66	61	81	72	66	61	71	65	61		69	64	60		68
7	78	68	61	57	77	67	61	56	66	60	56		65	60	56		64
8	74	64	57	52	73	63	57	52	62	56	52		61	56	52		60
9	70	60	53	49	69	59	53	49	58	52	48		57	52	48		56
10	67	56	50	45	66	56	49	45	55	49	45		54	49	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	44733
5°	43936
10°	41594
15°	37934
20°	33533
25°	29131
30°	24991
35°	20826
40°	15515
45°	9489
50°	4401
55°	3441
60°	3289
65°	3009
70°	2821
75°	2711
80°	2399
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9489 cd/sqm

TEST NUMBER: P1250866

CATALOG NUMBER: P3AS02R459030DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.7	8.8
10°-20°	46.5	22.0
20°-30°	55.3	26.2
30°-40°	48.0	22.8
40°-50°	24.1	11.4
50°-60°	8.4	4.0
60°-70°	5.8	2.8
70°-80°	3.3	1.5
80°-90°	1.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	120.4	57.1
0°-40°	168.4	79.8
0°-60°	200.9	95.2
0°-90°	211.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	211.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	204	
5°	200	19
15°	167	47
25°	120	55
35°	78	48
45°	31	24
55°	9	8
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1250866

CATALOG NUMBER: P3AS02R459030DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	204.0
2.5°	203.0
5°	199.6
7.5°	194.3
10°	186.8
12.5°	177.5
15°	167.1
17.5°	155.4
20°	143.7
22.5°	131.8
25°	120.4
27.5°	109.4
30°	98.7
32.5°	88.5
35°	77.8
37.5°	66.4
40°	54.2
42.5°	42.3
45°	30.6
47.5°	20.2
50°	12.9
52.5°	10.0
55°	9.0
57.5°	8.3
60°	7.5
62.5°	6.8
65°	5.8
67.5°	5.1
70°	4.4
72.5°	3.6
75°	3.2
77.5°	2.4
80°	1.9
82.5°	1.5
85°	0.7
87.5°	0.5
90°	0.0

(END OF REPORT)