

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249791

Luminaire Tested: P3AS17R609027DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249791
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R609027DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R60 optic, 2700K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1554.0 lumens
Efficiency: N/A
Efficacy: 73.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249791

CATALOG NUMBER: P3AS17R609027DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1249791

CATALOG NUMBER: P3AS17R609027DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	100	98		97
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	96	91	88	101	95	90	87	92	89	85		90	87	84		88
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83
5	93	84	79	74	91	84	78	74	82	77	73		80	76	73		79
6	88	79	73	69	87	79	73	69	77	72	68		76	71	68		74
7	84	75	69	64	82	74	68	64	73	68	64		71	67	64		70
8	80	70	64	60	78	70	64	60	69	64	60		68	63	60		67
9	76	66	61	57	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	371089
5°	356372
10°	366905
15°	371625
20°	328142
25°	276548
30°	224288
35°	146080
40°	67097
45°	25708
50°	8597
55°	2294
60°	2105
65°	1868
70°	1539
75°	2033
80°	1515
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 25708 cd/sqm

TEST NUMBER: P1249791

CATALOG NUMBER: P3AS17R609027DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.8	10.0
10°-20°	448.3	28.8
20°-30°	522.9	33.6
30°-40°	337.4	21.7
40°-50°	75.6	4.9
50°-60°	7.5	0.5
60°-70°	3.6	0.2
70°-80°	2.1	0.1
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1127.0	72.5
0°-40°	1464.4	94.2
0°-60°	1547.5	99.6
0°-90°	1554.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1554.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1692	
5°	1619	156
15°	1637	448
25°	1143	523
35°	546	337
45°	83	76
55°	6	8
65°	4	4
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1249791

CATALOG NUMBER: P3AS17R609027DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1692.3
2.5°	1664.6
5°	1619.0
7.5°	1616.6
10°	1647.8
12.5°	1668.3
15°	1637.0
17.5°	1543.3
20°	1406.2
22.5°	1263.2
25°	1143.0
27.5°	1025.2
30°	885.8
32.5°	722.3
35°	545.7
37.5°	372.6
40°	234.4
42.5°	140.6
45°	82.9
47.5°	48.1
50°	25.2
52.5°	8.4
55°	6.0
57.5°	4.8
60°	4.8
62.5°	3.6
65°	3.6
67.5°	3.6
70°	2.4
72.5°	2.4
75°	2.4
77.5°	1.2
80°	1.2
82.5°	1.2
85°	1.2
87.5°	0.0
90°	0.0

(END OF REPORT)