

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249807

Luminaire Tested: P3AS17R609027DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249807
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R609027DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R60 optic, 2700K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 486.0 lumens
Efficiency: N/A
Efficacy: 22.9 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249807
CATALOG NUMBER: P3AS17R609027DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1249807
 CATALOG NUMBER: P3AS17R609027DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82		
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74		
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67		
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61		
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56		
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51		
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47		
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44		
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	86265
5°	85296
10°	82341
15°	77798
20°	71710
25°	64939
30°	57654
35°	49255
40°	39159
45°	27631
50°	16511
55°	8334
60°	8026
65°	7368
70°	6796
75°	6524
80°	5935
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 27631 cd/sqm



TEST NUMBER: P1249807
 CATALOG NUMBER: P3AS17R609027DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.4	7.5
10°-20°	95.8	19.7
20°-30°	123.0	25.3
30°-40°	114.0	23.5
40°-50°	69.4	14.3
50°-60°	23.1	4.8
60°-70°	14.1	2.9
70°-80°	7.9	1.6
80°-90°	2.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	255.2	52.5
0°-40°	369.2	76.0
0°-60°	461.7	95.0
0°-90°	486.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	486.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	393	
5°	388	36
15°	343	96
25°	268	123
35°	184	114
45°	89	69
55°	22	23
65°	14	14
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P1249807
CATALOG NUMBER: P3AS17R609027DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	393.4
2.5°	391.7
5°	387.5
7.5°	379.9
10°	369.8
12.5°	357.5
15°	342.7
17.5°	325.6
20°	307.3
22.5°	287.8
25°	268.4
27.5°	248.3
30°	227.7
32.5°	207.0
35°	184.0
37.5°	159.9
40°	136.8
42.5°	112.7
45°	89.1
47.5°	69.0
50°	48.4
52.5°	28.9
55°	21.8
57.5°	20.1
60°	18.3
62.5°	15.9
65°	14.2
67.5°	12.4
70°	10.6
72.5°	8.8
75°	7.7
77.5°	5.9
80°	4.7
82.5°	2.9
85°	1.8
87.5°	1.2
90°	0.0

(END OF REPORT)