

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250884

Luminaire Tested: P3AS02R509030DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250884
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R509030DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 90CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 134.0 lumens
Efficiency: N/A
Efficacy: 37.2 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250884

CATALOG NUMBER: P3AS02R509030DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1250884

CATALOG NUMBER: P3AS02R509030DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	97	92	88	101	95	91	87	93	89	86		90	87	84		88
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84
5	93	85	80	76	92	84	79	75	83	78	74		81	77	74		79
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		75
7	85	76	70	66	84	75	70	66	74	69	66		73	69	65		72
8	81	72	66	62	80	71	66	62	70	65	62		69	65	62		68
9	78	68	63	59	76	68	62	59	67	62	59		66	62	58		65
10	74	65	59	56	73	65	59	56	64	59	55		63	59	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	42672
5°	41800
10°	39166
15°	35051
20°	29496
25°	22525
30°	14635
35°	8673
40°	5009
45°	2512
50°	921
55°	726
60°	658
65°	623
70°	641
75°	593
80°	631
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2512 cd/sqm

TEST NUMBER: P1250884

CATALOG NUMBER: P3AS02R509030DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.7	13.2
10°-20°	42.7	31.9
20°-30°	41.9	31.3
30°-40°	21.1	15.7
40°-50°	6.7	5.0
50°-60°	1.7	1.3
60°-70°	1.2	0.9
70°-80°	0.8	0.6
80°-90°	0.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	102.3	76.3
0°-40°	123.4	92.1
0°-60°	131.7	98.3
0°-90°	134.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	134.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	195	
5°	190	18
15°	154	43
25°	93	42
35°	32	21
45°	8	7
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1250884

CATALOG NUMBER: P3AS02R509030DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	194.6
2.5°	193.4
5°	189.9
7.5°	183.7
10°	175.9
12.5°	165.7
15°	154.4
17.5°	141.3
20°	126.4
22.5°	110.3
25°	93.1
27.5°	74.7
30°	57.8
32.5°	43.5
35°	32.4
37.5°	23.9
40°	17.5
42.5°	12.4
45°	8.1
47.5°	4.6
50°	2.7
52.5°	2.0
55°	1.9
57.5°	1.7
60°	1.5
62.5°	1.4
65°	1.2
67.5°	1.1
70°	1.0
72.5°	0.8
75°	0.7
77.5°	0.6
80°	0.5
82.5°	0.4
85°	0.2
87.5°	0.1
90°	0.0

(END OF REPORT)