

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249812

Luminaire Tested: P3AS17R609027DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249812
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R609027DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 2700K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 991.0 lumens
Efficiency: N/A
Efficacy: 46.7 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249812
CATALOG NUMBER: P3AS17R609027DE010 E3DLD1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1249812
 CATALOG NUMBER: P3AS17R609027DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91				91
2	105	99	94	90	103	98	93	89	94	90	87	91	88	85	88	86	84	82				82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74				74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67				67
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61				61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56				56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51				51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47				47
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44				44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41				41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	175907
5°	173937
10°	167910
15°	158639
20°	146219
25°	132419
30°	117562
35°	100465
40°	79864
45°	56316
50°	33636
55°	17013
60°	16358
65°	14995
70°	13848
75°	13217
80°	12123
85°	9057

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 56316 cd/sqm



TEST NUMBER: P1249812

CATALOG NUMBER: P3AS17R609027DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.3	7.5
10°-20°	195.3	19.7
20°-30°	250.8	25.3
30°-40°	232.5	23.5
40°-50°	141.5	14.3
50°-60°	47.2	4.8
60°-70°	28.7	2.9
70°-80°	16.1	1.6
80°-90°	4.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	520.3	52.5
0°-40°	752.8	76.0
0°-60°	941.5	95.0
0°-90°	991.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	991.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	802	
5°	790	74
15°	699	195
25°	547	251
35°	375	233
45°	182	142
55°	44	47
65°	29	29
75°	16	16
85°	4	5
90°	0	



TEST NUMBER: P1249812
CATALOG NUMBER: P3AS17R609027DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	802.2
2.5°	798.6
5°	790.2
7.5°	774.6
10°	754.1
12.5°	728.9
15°	698.8
17.5°	663.9
20°	626.6
22.5°	587.0
25°	547.3
27.5°	506.4
30°	464.3
32.5°	422.2
35°	375.3
37.5°	326.0
40°	279.0
42.5°	229.7
45°	181.6
47.5°	140.7
50°	98.6
52.5°	58.9
55°	44.5
57.5°	40.9
60°	37.3
62.5°	32.5
65°	28.9
67.5°	25.3
70°	21.6
72.5°	18.0
75°	15.6
77.5°	12.0
80°	9.6
82.5°	6.0
85°	3.6
87.5°	2.4
90°	0.0

(END OF REPORT)