

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249814

Luminaire Tested: P3AS17R609027DE010 E3DLP1H

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1249814  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R609027DE010 E3DLP1H  
Description: 3in Adjustable LED luminaire with, R60 optic, 2700K CCT AND, 90CRI , E3DLP1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 874.0 lumens  
Efficiency: N/A  
Efficacy: 41.2 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1249814  
CATALOG NUMBER: P3AS17R609027DE010 E3DLP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1249814  
 CATALOG NUMBER: P3AS17R609027DE010 E3DLP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85				85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78				78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66				66
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62				62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	58				58
8	77	67	60	56	75	66	60	56	65	60	56	64	59	55	63	58	55	54				54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50				50
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47				47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	221495
5°	216530
10°	202713
15°	181863
20°	156394
25°	129322
30°	102193
35°	75891
40°	52269
45°	32779
50°	18012
55°	10552
60°	9473
65°	8094
70°	6924
75°	7117
80°	6061
85°	6038

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 32779 cd/sqm



TEST NUMBER: P1249814  
 CATALOG NUMBER: P3AS17R609027DE010 E3DLP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	91.6	10.5
10°-20°	222.5	25.5
20°-30°	244.0	27.9
30°-40°	177.8	20.3
40°-50°	84.0	9.6
50°-60°	27.5	3.1
60°-70°	15.6	1.8
70°-80°	8.4	1.0
80°-90°	2.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	558.1	63.9
0°-40°	735.9	84.2
0°-60°	847.4	97.0
0°-90°	874.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	874.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1010	
5°	984	92
15°	801	222
25°	534	244
35°	284	178
45°	106	84
55°	28	27
65°	16	16
75°	8	8
85°	2	3
90°	0	



TEST NUMBER: P1249814  
CATALOG NUMBER: P3AS17R609027DE010 E3DLP1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1010.1
2.5°	1004.1
5°	983.7
7.5°	952.5
10°	910.4
12.5°	860.0
15°	801.1
17.5°	737.5
20°	670.2
22.5°	601.7
25°	534.5
27.5°	467.2
30°	403.6
32.5°	342.3
35°	283.5
37.5°	230.6
40°	182.6
42.5°	140.5
45°	105.7
47.5°	76.9
50°	52.8
52.5°	34.8
55°	27.6
57.5°	24.0
60°	21.6
62.5°	18.0
65°	15.6
67.5°	13.2
70°	10.8
72.5°	9.6
75°	8.4
77.5°	6.0
80°	4.8
82.5°	3.6
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)