

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250919

Luminaire Tested: P3AS02R559030DE010 E3DLD1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1250919  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R559030DE010 E3DLD1GPH  
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 90CRI , E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 101.0 lumens  
Efficiency: N/A  
Efficacy: 28.0 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1250919  
CATALOG NUMBER: P3AS02R559030DE010 E3DLD1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1250919  
 CATALOG NUMBER: P3AS02R559030DE010 E3DLD1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91			
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82			
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74			
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68			
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	64	62			
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57			
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52			
8	73	62	55	51	72	62	55	51	60	55	50	59	54	50	58	53	50	48			
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45			
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	18990
5°	18754
10°	18013
15°	16845
20°	15355
25°	13719
30°	12002
35°	9958
40°	7843
45°	5334
50°	3241
55°	1682
60°	1579
65°	1505
70°	1346
75°	1186
80°	1263
85°	1006

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 5334 cd/sqm



TEST NUMBER: P1250919  
 CATALOG NUMBER: P3AS02R559030DE010 E3DLD1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	8.0	7.9
10°-20°	20.7	20.5
20°-30°	26.0	25.7
30°-40°	23.2	22.9
40°-50°	13.6	13.4
50°-60°	4.7	4.6
60°-70°	2.8	2.8
70°-80°	1.6	1.6
80°-90°	0.5	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	54.7	54.2
0°-40°	77.9	77.1
0°-60°	96.1	95.2
0°-90°	101.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	101.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	87	
5°	85	8
15°	74	21
25°	57	26
35°	37	23
45°	17	14
55°	4	5
65°	3	3
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P1250919  
CATALOG NUMBER: P3AS02R559030DE010 E3DLD1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	86.6
2.5°	86.1
5°	85.2
7.5°	83.3
10°	80.9
12.5°	77.9
15°	74.2
17.5°	70.3
20°	65.8
22.5°	61.3
25°	56.7
27.5°	52.0
30°	47.4
32.5°	42.3
35°	37.2
37.5°	32.2
40°	27.4
42.5°	22.3
45°	17.2
47.5°	13.1
50°	9.5
52.5°	6.2
55°	4.4
57.5°	3.9
60°	3.6
62.5°	3.2
65°	2.9
67.5°	2.5
70°	2.1
72.5°	1.8
75°	1.4
77.5°	1.2
80°	1.0
82.5°	0.6
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)