

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250924

Luminaire Tested: P3AS02R559030DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250924
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R559030DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 90CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 206.0 lumens
Efficiency: N/A
Efficacy: 57.2 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250924
CATALOG NUMBER: P3AS02R559030DE010 E3DLD1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1250924

CATALOG NUMBER: P3AS02R559030DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	102	103	100	98	99	97	96	95	94	93	91			91
2	105	100	95	91	103	98	93	90	94	91	88	91	88	86	89	86	84	82			82
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74			74
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68			68
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	64	62			62
6	82	72	65	60	80	71	64	60	69	64	59	68	63	59	66	62	58	57			57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52			52
8	73	62	55	51	72	62	55	51	60	55	50	59	54	50	58	53	50	48			48
9	69	58	51	47	68	58	51	47	57	51	47	56	50	46	55	50	46	45			45
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42			42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	38725
5°	38235
10°	36739
15°	34348
20°	31339
25°	27969
30°	24459
35°	20318
40°	16030
45°	10854
50°	6652
55°	3441
60°	3201
65°	3009
70°	2821
75°	2457
80°	2399
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10854 cd/sqm



TEST NUMBER: P1250924

CATALOG NUMBER: P3AS02R559030DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	16.3	7.9
10°-20°	42.3	20.5
20°-30°	53.0	25.7
30°-40°	47.3	23.0
40°-50°	27.7	13.4
50°-60°	9.6	4.6
60°-70°	5.8	2.8
70°-80°	3.2	1.5
80°-90°	0.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	111.6	54.2
0°-40°	158.9	77.1
0°-60°	196.1	95.2
0°-90°	206.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	206.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	177	
5°	174	16
15°	151	42
25°	116	53
35°	76	47
45°	35	28
55°	9	10
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1250924
CATALOG NUMBER: P3AS02R559030DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	176.6
2.5°	175.7
5°	173.7
7.5°	169.8
10°	165.0
12.5°	158.9
15°	151.3
17.5°	143.3
20°	134.3
22.5°	125.1
25°	115.6
27.5°	106.1
30°	96.6
32.5°	86.4
35°	75.9
37.5°	65.7
40°	56.0
42.5°	45.5
45°	35.0
47.5°	26.8
50°	19.5
52.5°	12.7
55°	9.0
57.5°	8.0
60°	7.3
62.5°	6.6
65°	5.8
67.5°	5.1
70°	4.4
72.5°	3.6
75°	2.9
77.5°	2.4
80°	1.9
82.5°	1.2
85°	0.7
87.5°	0.5
90°	0.0

(END OF REPORT)