

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250958

Luminaire Tested: P3AS02R609030DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250958
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R609030DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 256.0 lumens
Efficiency: N/A
Efficacy: 71.1 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250958

CATALOG NUMBER: P3AS02R609030DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1250958

CATALOG NUMBER: P3AS02R609030DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	77	68	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	60456
5°	59872
10°	58137
15°	54461
20°	48211
25°	40333
30°	31600
35°	22914
40°	15257
45°	9520
50°	5151
55°	1491
60°	1403
65°	1245
70°	1218
75°	1271
80°	1263
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9520 cd/sqm

TEST NUMBER: P1250958

CATALOG NUMBER: P3AS02R609030DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.6	10.0
10°-20°	66.6	26.0
20°-30°	75.9	29.6
30°-40°	53.8	21.0
40°-50°	24.4	9.5
50°-60°	5.2	2.0
60°-70°	2.5	1.0
70°-80°	1.5	0.6
80°-90°	0.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	168.0	65.6
0°-40°	221.8	86.7
0°-60°	251.5	98.2
0°-90°	256.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	256.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	276	
5°	272	26
15°	240	67
25°	167	76
35°	86	54
45°	31	24
55°	4	5
65°	2	2
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1250958

CATALOG NUMBER: P3AS02R609030DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	275.7
2.5°	274.7
5°	272.0
7.5°	267.4
10°	261.1
12.5°	252.1
15°	239.9
17.5°	224.6
20°	206.6
22.5°	187.1
25°	166.7
27.5°	145.7
30°	124.8
32.5°	104.9
35°	85.6
37.5°	68.6
40°	53.3
42.5°	40.4
45°	30.7
47.5°	22.9
50°	15.1
52.5°	7.1
55°	3.9
57.5°	3.4
60°	3.2
62.5°	2.9
65°	2.4
67.5°	2.2
70°	1.9
72.5°	1.7
75°	1.5
77.5°	1.2
80°	1.0
82.5°	0.7
85°	0.5
87.5°	0.2
90°	0.0

(END OF REPORT)