

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249852

Luminaire Tested: P3AS17R709027DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249852
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R709027DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 90CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1504.0 lumens
Efficiency: N/A
Efficacy: 70.9 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249852

CATALOG NUMBER: P3AS17R709027DE010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1249852

CATALOG NUMBER: P3AS17R709027DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85
4	95	87	81	77	94	86	81	76	84	79	75		82	78	75		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66
8	76	66	59	55	75	65	59	55	64	58	55		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	50		58
10	68	58	52	47	67	57	51	47	56	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	298660
5°	284987
10°	271137
15°	263883
20°	254145
25°	240522
30°	223705
35°	187920
40°	121113
45°	56285
50°	14771
55°	3670
60°	3684
65°	3113
70°	3077
75°	3050
80°	3031
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 56285 cd/sqm

TEST NUMBER: P1249852

CATALOG NUMBER: P3AS17R709027DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.2	8.1
10°-20°	326.6	21.7
20°-30°	456.3	30.3
30°-40°	423.1	28.1
40°-50°	151.7	10.1
50°-60°	12.8	0.9
60°-70°	6.4	0.4
70°-80°	4.1	0.3
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	904.2	60.1
0°-40°	1327.3	88.3
0°-60°	1491.8	99.2
0°-90°	1504.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1504.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1362	
5°	1295	121
15°	1162	327
25°	994	456
35°	702	423
45°	182	152
55°	10	13
65°	6	6
75°	4	4
85°	1	2
90°	0	

TEST NUMBER: P1249852

CATALOG NUMBER: P3AS17R709027DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1362.0
2.5°	1341.5
5°	1294.7
7.5°	1251.4
10°	1217.7
12.5°	1190.1
15°	1162.4
17.5°	1128.8
20°	1089.1
22.5°	1043.4
25°	994.1
27.5°	943.6
30°	883.5
32.5°	806.6
35°	702.0
37.5°	568.6
40°	423.1
42.5°	288.5
45°	181.5
47.5°	101.0
50°	43.3
52.5°	14.4
55°	9.6
57.5°	8.4
60°	8.4
62.5°	7.2
65°	6.0
67.5°	6.0
70°	4.8
72.5°	4.8
75°	3.6
77.5°	3.6
80°	2.4
82.5°	2.4
85°	1.2
87.5°	1.2
90°	0.0

(END OF REPORT)