

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249867

Luminaire Tested: P3AS17R709027DE010 E3DLP1LI

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1249867  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R709027DE010 E3DLP1LI  
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 90CRI , E3DLP1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 863.9 lumens  
Efficiency: N/A  
Efficacy: 40.8 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1249867  
CATALOG NUMBER: P3AS17R709027DE010 E3DLP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P1249867  
 CATALOG NUMBER: P3AS17R709027DE010 E3DLP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92				92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84				84
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77				77
4	95	86	80	76	93	85	80	75	83	78	74	81	77	73	79	76	73	71				71
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65				65
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	65	62	61				61
7	80	70	64	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56				56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52				52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49				49
10	69	58	52	48	67	58	52	48	57	51	48	56	51	48	55	51	47	46				46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	202659
5°	198943
10°	187594
15°	170239
20°	148926
25°	125620
30°	102851
35°	79799
40°	57107
45°	36159
50°	18046
55°	11010
60°	9473
65°	8717
70°	7694
75°	7117
80°	6061
85°	6038

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 36159 cd/sqm



TEST NUMBER: P1249867  
 CATALOG NUMBER: P3AS17R709027DE010 E3DLP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	84.3	9.8
10°-20°	208.7	24.2
20°-30°	237.7	27.5
30°-40°	185.8	21.5
40°-50°	91.3	10.6
50°-60°	28.1	3.2
60°-70°	16.6	1.9
70°-80°	8.9	1.0
80°-90°	2.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	530.7	61.4
0°-40°	716.5	82.9
0°-60°	835.9	96.7
0°-90°	863.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	863.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	924	
5°	904	84
15°	750	209
25°	519	238
35°	298	186
45°	117	91
55°	29	28
65°	17	17
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P1249867  
CATALOG NUMBER: P3AS17R709027DE010 E3DLP1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	924.2
2.5°	919.4
5°	903.8
7.5°	878.5
10°	842.5
12.5°	800.4
15°	749.9
17.5°	695.9
20°	638.2
22.5°	578.1
25°	519.2
27.5°	461.5
30°	406.2
32.5°	350.9
35°	298.1
37.5°	247.6
40°	199.5
42.5°	155.0
45°	116.6
47.5°	81.7
50°	52.9
52.5°	34.9
55°	28.8
57.5°	25.2
60°	21.6
62.5°	19.2
65°	16.8
67.5°	14.4
70°	12.0
72.5°	9.6
75°	8.4
77.5°	7.2
80°	4.8
82.5°	3.6
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)