

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249869

Luminaire Tested: P3AS17R709027DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249869
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R709027DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 90CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1209.9 lumens
Efficiency: N/A
Efficacy: 57.1 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249869
CATALOG NUMBER: P3AS17R709027DE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1249869
 CATALOG NUMBER: P3AS17R709027DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92	92	92	92
2	106	101	96	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	84	84
3	100	93	88	83	98	92	87	82	89	85	81	86	83	80	84	81	79	77	77	77	77
4	94	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	70	70	70	70
5	89	80	73	69	87	79	73	68	77	72	68	75	71	67	74	70	66	65	65	65	65
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60	60	60	60
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55	55	55	55
8	75	65	58	53	74	64	58	53	63	57	53	62	57	53	61	56	53	51	51	51	51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48	48	48	48
10	67	57	50	46	66	56	50	46	55	50	46	55	49	46	54	49	46	44	44	44	44

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	234236
5°	231432
10°	224756
15°	215234
20°	201618
25°	183156
30°	158202
35°	126083
40°	91829
45°	60378
50°	28281
55°	8717
60°	8420
65°	8094
70°	7694
75°	8133
80°	7577
85°	6038

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 60378 cd/sqm



TEST NUMBER: P1249869
 CATALOG NUMBER: P3AS17R709027DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.0	8.2
10°-20°	265.3	21.9
20°-30°	344.9	28.5
30°-40°	292.6	24.2
40°-50°	150.9	12.5
50°-60°	29.1	2.4
60°-70°	15.7	1.3
70°-80°	9.7	0.8
80°-90°	2.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	709.2	58.6
0°-40°	1001.8	82.8
0°-60°	1181.7	97.7
0°-90°	1209.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1209.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1068	
5°	1051	99
15°	948	265
25°	757	345
35°	471	293
45°	195	151
55°	23	29
65°	16	16
75°	10	10
85°	2	3
90°	0	



TEST NUMBER: P1249869
CATALOG NUMBER: P3AS17R709027DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1068.2
2.5°	1064.6
5°	1051.4
7.5°	1032.2
10°	1009.4
12.5°	980.5
15°	948.1
17.5°	908.4
20°	864.0
22.5°	813.5
25°	757.0
27.5°	693.3
30°	624.8
32.5°	549.1
35°	471.0
37.5°	394.1
40°	320.8
42.5°	252.3
45°	194.7
47.5°	143.0
50°	82.9
52.5°	36.0
55°	22.8
57.5°	21.6
60°	19.2
62.5°	18.0
65°	15.6
67.5°	14.4
70°	12.0
72.5°	10.8
75°	9.6
77.5°	7.2
80°	6.0
82.5°	3.6
85°	2.4
87.5°	1.2
90°	0.0

(END OF REPORT)