

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250990

Luminaire Tested: P3AS02R709030DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250990
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R709030DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 90CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 305.0 lumens
Efficiency: N/A
Efficacy: 84.7 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250990

CATALOG NUMBER: P3AS02R709030DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1250990

CATALOG NUMBER: P3AS02R709030DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85
4	95	87	81	77	94	86	81	76	84	79	75		82	78	75		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66
8	76	66	59	55	75	65	59	55	64	58	55		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	50		58
10	68	58	52	47	67	57	51	47	56	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	60565
5°	57781
10°	54976
15°	53508
20°	51548
25°	48777
30°	45374
35°	38119
40°	24560
45°	11412
50°	3002
55°	765
60°	746
65°	623
70°	641
75°	593
80°	631
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11412 cd/sqm

TEST NUMBER: P1250990

CATALOG NUMBER: P3AS02R709030DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	24.6	8.1
10°-20°	66.2	21.7
20°-30°	92.6	30.3
30°-40°	85.8	28.1
40°-50°	30.8	10.1
50°-60°	2.6	0.9
60°-70°	1.3	0.4
70°-80°	0.8	0.3
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	183.4	60.1
0°-40°	269.2	88.3
0°-60°	302.6	99.2
0°-90°	305.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	305.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	276	
5°	262	25
15°	236	66
25°	202	93
35°	142	86
45°	37	31
55°	2	3
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1250990

CATALOG NUMBER: P3AS02R709030DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	276.2
2.5°	272.1
5°	262.5
7.5°	253.8
10°	246.9
12.5°	241.3
15°	235.7
17.5°	228.9
20°	220.9
22.5°	211.6
25°	201.6
27.5°	191.4
30°	179.2
32.5°	163.6
35°	142.4
37.5°	115.3
40°	85.8
42.5°	58.5
45°	36.8
47.5°	20.5
50°	8.8
52.5°	2.9
55°	2.0
57.5°	1.7
60°	1.7
62.5°	1.5
65°	1.2
67.5°	1.2
70°	1.0
72.5°	1.0
75°	0.7
77.5°	0.7
80°	0.5
82.5°	0.5
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)