

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251066

Luminaire Tested: P3AS05R129030DE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251066
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R129030DE010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R12 optic, 3000K CCT AND, 90CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 378.0 lumens
Efficiency: N/A
Efficacy: 49.7 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251066
CATALOG NUMBER: P3AS05R129030DE010 E3DLD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1251066
 CATALOG NUMBER: P3AS05R129030DE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91			91
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			83
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76			76
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			70
5	89	80	73	68	87	79	73	68	77	72	67	75	70	67	74	69	66	65			65
6	84	74	68	63	83	73	67	63	72	66	62	70	66	62	69	65	61	60			60
7	80	69	63	58	78	69	63	58	67	62	58	66	61	57	65	61	57	56			56
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52			52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49			49
10	68	58	52	48	67	57	51	47	57	51	47	56	51	47	55	50	47	46			46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	95343
5°	92758
10°	84768
15°	74257
20°	63706
25°	53180
30°	42564
35°	31909
40°	23158
45°	15133
50°	9484
55°	6423
60°	5657
65°	5241
70°	4937
75°	4490
80°	4293
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15133 cd/sqm



TEST NUMBER: P1251066
 CATALOG NUMBER: P3AS05R129030DE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.9	10.3
10°-20°	91.1	24.1
20°-30°	100.4	26.6
30°-40°	75.2	19.9
40°-50°	39.0	10.3
50°-60°	16.2	4.3
60°-70°	10.0	2.6
70°-80°	5.6	1.5
80°-90°	1.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	230.4	61.0
0°-40°	305.6	80.8
0°-60°	360.7	95.4
0°-90°	378.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	378.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	435	
5°	421	39
15°	327	91
25°	220	100
35°	119	75
45°	49	39
55°	17	16
65°	10	10
75°	5	6
85°	1	2
90°	0	



TEST NUMBER: P1251066
CATALOG NUMBER: P3AS05R129030DE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	434.8
1°	435.3
2°	433.9
3°	431.0
4°	426.7
5°	421.4
6°	414.7
7°	407.5
8°	398.9
9°	389.8
10°	380.7
12.5°	354.4
15°	327.1
17.5°	299.8
20°	273.0
22.5°	245.7
25°	219.8
27.5°	193.9
30°	168.1
32.5°	142.7
35°	119.2
37.5°	99.1
40°	80.9
42.5°	64.2
45°	48.8
47.5°	36.9
50°	27.8
52.5°	20.6
55°	16.8
57.5°	14.8
60°	12.9
62.5°	11.5
65°	10.1
67.5°	8.6
70°	7.7
72.5°	6.2
75°	5.3
77.5°	4.3
80°	3.4
82.5°	2.4
85°	1.4
87.5°	0.5
90°	0.0

(END OF REPORT)