

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249915

Luminaire Tested: P3AS20R209027D010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249915
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R209027D010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R20 optic, 2700K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1978.0 lumens
Efficiency: N/A
Efficacy: 68.7 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249915

CATALOG NUMBER: P3AS20R209027D010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1249915

CATALOG NUMBER: P3AS20R209027D010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	114	112	110		113	111	110	108		107	106	105		104	103	102		100	100	99
2	112	109	106	104		110	107	105	103		104	102	101		101	100	98		99	98	96
3	109	105	102	99		107	104	101	98		101	99	97		99	97	95		97	95	94
4	106	101	98	95		105	100	97	95		99	96	94		97	95	93		95	93	92
5	104	98	95	92		102	98	94	92		96	93	91		95	92	90		93	91	90
6	101	96	92	89		100	95	92	89		94	91	89		93	90	88		92	89	88
7	99	93	90	87		98	93	89	87		92	89	86		91	88	86		90	87	86
8	97	91	87	85		96	91	87	85		90	87	85		89	86	84		88	86	84
9	95	89	85	83		94	89	85	83		88	85	83		87	84	83		87	84	82
10	93	87	84	81		92	87	83	81		86	83	81		86	83	81		85	83	81

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3000461
5°	2526254
10°	1577882
15°	589901
20°	202481
25°	84392
30°	39753
35°	17802
40°	8416
45°	4311
50°	1569
55°	306
60°	351
65°	415
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4311 cd/sqm

TEST NUMBER: P1249915

CATALOG NUMBER: P3AS20R209027D010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	954.4	48.3
10°-20°	786.1	39.7
20°-30°	178.6	9.0
30°-40°	45.5	2.3
40°-50°	11.4	0.6
50°-60°	1.5	0.1
60°-70°	0.5	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1919.2	97.0
0°-40°	1964.6	99.3
0°-60°	1977.5	100.0
0°-90°	1978.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1978.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13683	
5°	11477	954
15°	2598	786
25°	349	179
35°	66	45
45°	14	11
55°	1	1
65°	1	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1249915

CATALOG NUMBER: P3AS20R209027D010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	13683.2
1°	13567.2
2°	13225.4
3°	12735.1
4°	12133.4
5°	11476.8
6°	10745.2
7°	9937.8
8°	8995.8
9°	8062.4
10°	7086.4
11°	6047.7
12°	5010.7
13°	4132.1
14°	3292.2
15°	2598.5
16°	2051.0
17°	1617.9
18°	1300.0
19°	1057.2
20°	867.7
21°	725.4
22°	605.5
23°	503.5
24°	419.9
25°	348.8
27.5°	228.1
30°	157.0
32.5°	96.7
35°	66.5
37.5°	42.5
40°	29.4
42.5°	20.1
45°	13.9
47.5°	9.3
50°	4.6
52.5°	2.3
55°	0.8
57.5°	0.8
60°	0.8
62.5°	0.8
65°	0.8
67.5°	0.0
70°	0.0
72.5°	0.0



TEST NUMBER: P1249915

CATALOG NUMBER: P3AS20R209027D010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)