

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251101

Luminaire Tested: P3AS05R159030DE010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251101
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R159030DE010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 90CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 308.0 lumens
Efficiency: N/A
Efficacy: 42.8 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251101

CATALOG NUMBER: P3AS05R159030DE010 E3DLP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1251101

CATALOG NUMBER: P3AS05R159030DE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	93						
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86						
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80						
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75						
5	93	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70						
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66						
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62						
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59						
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56						
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	57	54	53						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	132818
5°	122760
10°	97994
15°	74030
20°	56378
25°	42970
30°	30764
35°	20077
40°	12309
45°	7443
50°	4947
55°	3823
60°	3289
65°	2854
70°	2565
75°	2542
80°	1894
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7443 cd/sqm

TEST NUMBER: P1251101

CATALOG NUMBER: P3AS05R159030DE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.4	16.0
10°-20°	91.1	29.6
20°-30°	81.1	26.3
30°-40°	48.0	15.6
40°-50°	19.7	6.4
50°-60°	9.2	3.0
60°-70°	5.6	1.8
70°-80°	3.0	1.0
80°-90°	0.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	221.7	72.0
0°-40°	269.7	87.6
0°-60°	298.6	97.0
0°-90°	308.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	308.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	606	
5°	558	49
15°	326	91
25°	178	81
35°	75	48
45°	24	20
55°	10	9
65°	6	6
75°	3	3
85°	0	1
90°	0	

TEST NUMBER: P1251101

CATALOG NUMBER: P3AS05R159030DE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	605.7
1°	604.2
2°	599.7
3°	590.7
4°	575.7
5°	557.7
6°	538.2
7°	515.2
8°	491.2
9°	466.6
10°	440.1
12.5°	379.6
15°	326.1
17.5°	280.1
20°	241.6
22.5°	207.6
25°	177.6
27.5°	148.5
30°	121.5
32.5°	97.0
35°	75.0
37.5°	57.5
40°	43.0
42.5°	32.0
45°	24.0
47.5°	18.5
50°	14.5
52.5°	12.0
55°	10.0
57.5°	8.5
60°	7.5
62.5°	6.5
65°	5.5
67.5°	5.0
70°	4.0
72.5°	3.5
75°	3.0
77.5°	2.0
80°	1.5
82.5°	1.0
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)