

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251106

Luminaire Tested: P3AS05R159030DE010 E3PHLD1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251106
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R159030DE010 E3PHLD1MW
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 90CRI , E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 330.0 lumens
Efficiency: N/A
Efficacy: 45.8 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.66
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251106
CATALOG NUMBER: P3AS05R159030DE010 E3PHLD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1251106
 CATALOG NUMBER: P3AS05R159030DE010 E3PHLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90	90	90	90
2	104	98	93	89	102	97	92	88	93	89	86	90	87	84	87	85	82	80	80	80	80
3	98	90	84	79	96	88	83	78	85	81	77	83	79	75	81	77	74	72	72	72	72
4	92	82	76	70	90	81	75	70	79	73	69	77	72	68	75	71	67	66	66	66	66
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60	60	60	60
6	81	71	63	58	79	70	63	58	68	62	58	67	61	57	65	60	57	55	55	55	55
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51	51	51	51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47	47	47	47
9	69	58	51	47	68	57	51	46	56	50	46	55	50	46	54	49	46	44	44	44	44
10	65	54	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42	42	42	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	96023
5°	90028
10°	73813
15°	57344
20°	45271
25°	36075
30°	28966
35°	23637
40°	19465
45°	16374
50°	14089
55°	12157
60°	10789
65°	9391
70°	8335
75°	6778
80°	5430
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16374 cd/sqm



TEST NUMBER: P1251106
 CATALOG NUMBER: P3AS05R159030DE010 E3PHLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.5	11.1
10°-20°	70.8	21.4
20°-30°	68.8	20.8
30°-40°	55.6	16.8
40°-50°	41.3	12.5
50°-60°	28.8	8.7
60°-70°	18.1	5.5
70°-80°	8.6	2.6
80°-90°	1.6	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	176.1	53.4
0°-40°	231.7	70.2
0°-60°	301.8	91.5
0°-90°	330.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	330.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	438	
5°	409	37
15°	253	71
25°	149	69
35°	88	56
45°	53	41
55°	32	29
65°	18	18
75°	8	9
85°	1	2
90°	0	



TEST NUMBER: P1251106
CATALOG NUMBER: P3AS05R159030DE010 E3PHLD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	437.9
2.5°	430.7
5°	409.0
7.5°	374.2
10°	331.5
12.5°	289.5
15°	252.6
17.5°	221.5
20°	194.0
22.5°	170.1
25°	149.1
27.5°	130.3
30°	114.4
32.5°	100.6
35°	88.3
37.5°	77.5
40°	68.0
42.5°	60.1
45°	52.8
47.5°	47.1
50°	41.3
52.5°	36.2
55°	31.8
57.5°	28.2
60°	24.6
62.5°	21.0
65°	18.1
67.5°	15.2
70°	13.0
72.5°	10.1
75°	8.0
77.5°	5.8
80°	4.3
82.5°	2.2
85°	1.4
87.5°	0.0
90°	0.0

(END OF REPORT)