

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1249975

Luminaire Tested: P3AS20R309027D010 E3DL1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1249975
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R309027D010 E3DL1H
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 90CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1671.0 lumens
Efficiency: N/A
Efficacy: 58.0 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1249975
CATALOG NUMBER: P3AS20R309027D010 E3DL1H

Luminous Intensity Polar Plot





TEST NUMBER: P1249975
 CATALOG NUMBER: P3AS20R309027D010 E3DL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20					
RC	80				70				50				30				10			0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	93	92	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	91	89	87	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	88	85	83	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	86	83	81	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	85	82	79	78
6	94	86	81	78	92	85	81	77	84	80	77	83	79	76	81	78	76	75	81	78	76	75
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	79	75	73	71	79	75	73	71
8	87	79	74	71	86	79	74	71	78	73	70	77	73	70	76	72	70	69	76	72	70	69
9	84	76	71	68	83	75	71	68	75	70	67	74	70	67	73	70	67	66	73	70	67	66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	63	71	67	65	63

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	975075
5°	928085
10°	780636
15°	562977
20°	349190
25°	198592
30°	110321
35°	60017
40°	31631
45°	17118
50°	9143
55°	6040
60°	5526
65°	5707
70°	5065
75°	3982
80°	4041
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17118 cd/sqm



TEST NUMBER: P1249975
 CATALOG NUMBER: P3AS20R309027D010 E3DL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	379.6	22.7
10°-20°	674.9	40.4
20°-30°	390.0	23.3
30°-40°	148.0	8.9
40°-50°	45.4	2.7
50°-60°	15.3	0.9
60°-70°	10.3	0.6
70°-80°	5.6	0.3
80°-90°	1.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1444.5	86.5
0°-40°	1592.6	95.3
0°-60°	1653.3	98.9
0°-90°	1671.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1671.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4447	
5°	4216	380
15°	2480	675
25°	821	390
35°	224	148
45°	55	45
55°	16	15
65°	11	10
75°	5	6
85°	2	2
90°	0	

TEST NUMBER: P1249975
CATALOG NUMBER: P3AS20R309027D010 E3DL1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	4446.7
1°	4443.6
2°	4416.7
3°	4366.2
4°	4303.1
5°	4216.3
6°	4105.8
7°	3982.6
8°	3845.3
9°	3681.1
10°	3505.9
11°	3316.5
12°	3116.0
13°	2906.1
14°	2693.0
15°	2479.9
17.5°	1955.8
20°	1496.4
22.5°	1109.7
25°	820.8
27.5°	596.7
30°	435.7
32.5°	314.1
35°	224.2
37.5°	156.3
40°	110.5
42.5°	77.3
45°	55.2
47.5°	37.9
50°	26.8
52.5°	18.9
55°	15.8
57.5°	14.2
60°	12.6
62.5°	11.0
65°	11.0
67.5°	9.5
70°	7.9
72.5°	6.3
75°	4.7
77.5°	4.7
80°	3.2
82.5°	3.2
85°	1.6
87.5°	0.0



TEST NUMBER: P1249975
CATALOG NUMBER: P3AS20R309027D010 E3DL1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)