

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251183

Luminaire Tested: P3AS05R309030DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251183
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R309030DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 90CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 199.9 lumens
Efficiency: N/A
Efficacy: 27.8 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251183

CATALOG NUMBER: P3AS05R309030DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1251183

CATALOG NUMBER: P3AS05R309030DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	86	79	74	92	84	79	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	77	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	47255
5°	46181
10°	42952
15°	38230
20°	32880
25°	27848
30°	23117
35°	18123
40°	12996
45°	8528
50°	4844
55°	3173
60°	3026
65°	2802
70°	2500
75°	2288
80°	2147
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8528 cd/sqm

TEST NUMBER: P1251183

CATALOG NUMBER: P3AS05R309030DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.5	9.7
10°-20°	46.8	23.4
20°-30°	52.7	26.4
30°-40°	42.1	21.1
40°-50°	21.6	10.8
50°-60°	8.1	4.1
60°-70°	5.3	2.7
70°-80°	2.9	1.4
80°-90°	0.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	119.0	59.5
0°-40°	161.1	80.6
0°-60°	190.9	95.5
0°-90°	199.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	199.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	216	
5°	210	19
15°	168	47
25°	115	53
35°	68	42
45°	28	22
55°	8	8
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1251183

CATALOG NUMBER: P3AS05R309030DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	215.5
1°	215.5
2°	214.7
3°	213.5
4°	211.8
5°	209.8
6°	207.4
7°	204.2
8°	200.8
9°	196.8
10°	192.9
11°	188.5
12°	183.8
13°	178.9
14°	173.8
15°	168.4
17.5°	154.6
20°	140.9
22.5°	127.6
25°	115.1
27.5°	102.8
30°	91.3
32.5°	79.5
35°	67.7
37.5°	56.2
40°	45.4
42.5°	35.8
45°	27.5
47.5°	20.4
50°	14.2
52.5°	10.1
55°	8.3
57.5°	7.6
60°	6.9
62.5°	6.1
65°	5.4
67.5°	4.7
70°	3.9
72.5°	3.2
75°	2.7
77.5°	2.2
80°	1.7
82.5°	1.2
85°	0.7
87.5°	0.2



TEST NUMBER: P1251183
CATALOG NUMBER: P3AS05R309030DE010 E3DLD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)