

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250014

Luminaire Tested: P3AS20R359027D010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250014
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R359027D010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 90CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 502.0 lumens
Efficiency: N/A
Efficacy: 17.4 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250014

CATALOG NUMBER: P3AS20R359027D010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1250014

CATALOG NUMBER: P3AS20R359027D010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	97	93	97	94	91		94	92	89		91
3	102	95	90	86	100	94	89	85	91	87	84		89	85	82		86
4	97	89	83	79	95	88	82	78	86	81	77		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	77	72	68	76	71	67		75	70	67		73
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	70	64	60	78	69	63	59	68	63	59		67	62	59		66
9	76	66	60	56	75	66	60	56	65	59	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	161347
5°	157385
10°	143885
15°	122135
20°	96678
25°	73117
30°	53223
35°	36005
40°	22127
45°	12714
50°	7642
55°	6193
60°	5438
65°	4825
70°	3975
75°	3897
80°	3915
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12714 cd/sqm

TEST NUMBER: P1250014

CATALOG NUMBER: P3AS20R359027D010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.1	13.2
10°-20°	148.3	29.5
20°-30°	138.7	27.6
30°-40°	84.9	16.9
40°-50°	33.5	6.7
50°-60°	14.7	2.9
60°-70°	9.2	1.8
70°-80°	4.9	1.0
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	353.1	70.3
0°-40°	438.0	87.3
0°-60°	486.3	96.9
0°-90°	502.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	502.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	736	
5°	715	66
15°	538	148
25°	302	139
35°	134	85
45°	41	33
55°	16	15
65°	9	9
75°	5	5
85°	2	2
90°	0	

TEST NUMBER: P1250014

CATALOG NUMBER: P3AS20R359027D010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	735.8
1°	736.6
2°	734.3
3°	729.7
4°	722.7
5°	715.0
6°	704.9
7°	693.3
8°	679.4
9°	664.0
10°	646.2
11°	627.6
12°	607.5
13°	585.9
14°	561.9
15°	538.0
17.5°	476.1
20°	414.3
22.5°	354.8
25°	302.2
27.5°	253.5
30°	210.2
32.5°	170.0
35°	134.5
37.5°	102.8
40°	77.3
42.5°	55.7
45°	41.0
47.5°	29.4
50°	22.4
52.5°	18.6
55°	16.2
57.5°	13.9
60°	12.4
62.5°	10.8
65°	9.3
67.5°	7.7
70°	6.2
72.5°	5.4
75°	4.6
77.5°	3.9
80°	3.1
82.5°	2.3
85°	1.5
87.5°	0.8



TEST NUMBER: P1250014

CATALOG NUMBER: P3AS20R359027D010 E3DLP1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)