

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250055

Luminaire Tested: P3AS20R459027D010 E3CD1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1250055
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-28)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R459027D010 E3CD1MB
Description: 3in Adjustable LED luminaire with, R45 optic, 2700K CCT AND, 90CRI , E3CD1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2116.0 lumens
Efficiency: N/A
Efficacy: 73.5 lumens/watt
Spacing Criteria (0/90/45): 0.72 / 0.72 / 0.66
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1250055

CATALOG NUMBER: P3AS20R459027D010 E3CD1MB

Luminous Intensity Polar Plot



TEST NUMBER: P1250055

CATALOG NUMBER: P3AS20R459027D010 E3CD1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91		
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	86		
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	88	86	84	82		
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	79		
6	94	87	82	78	93	86	81	78	85	80	77	83	80	77	82	79	76	75		
7	90	83	78	74	89	82	78	74	81	77	74	80	76	74	79	76	73	72		
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69		
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66		
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	64		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	917405
5°	922296
10°	893949
15°	749130
20°	572650
25°	348625
30°	145060
35°	46471
40°	14456
45°	2946
50°	2149
55°	2409
60°	2061
65°	2439
70°	2052
75°	2711
80°	2020
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2946 cd/sqm

TEST NUMBER: P1250055

CATALOG NUMBER: P3AS20R459027D010 E3CD1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	395.2	18.7
10°-20°	907.0	42.9
20°-30°	653.0	30.9
30°-40°	135.9	6.4
40°-50°	12.4	0.6
50°-60°	5.1	0.2
60°-70°	4.1	0.2
70°-80°	2.7	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1955.2	92.4
0°-40°	2091.0	98.8
0°-60°	2108.5	99.6
0°-90°	2116.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2116.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4184	
5°	4190	395
15°	3300	907
25°	1441	653
35°	174	136
45°	10	12
55°	6	5
65°	5	4
75°	3	3
85°	0	1
90°	0	

TEST NUMBER: P1250055

CATALOG NUMBER: P3AS20R459027D010 E3CD1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	4183.7
2.5°	4185.3
5°	4190.0
7.5°	4160.0
10°	4014.8
12.5°	3711.8
15°	3299.9
17.5°	2878.6
20°	2454.0
22.5°	1966.4
25°	1440.9
27.5°	950.0
30°	572.9
32.5°	320.4
35°	173.6
37.5°	97.8
40°	50.5
42.5°	22.1
45°	9.5
47.5°	6.3
50°	6.3
52.5°	6.3
55°	6.3
57.5°	4.7
60°	4.7
62.5°	4.7
65°	4.7
67.5°	3.2
70°	3.2
72.5°	3.2
75°	3.2
77.5°	1.6
80°	1.6
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)