

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1251290

Luminaire Tested: P3AS05R509030DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1251290
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R509030DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 90CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 694.9 lumens
Efficiency: N/A
Efficacy: 96.5 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1251290

CATALOG NUMBER: P3AS05R509030DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1251290

CATALOG NUMBER: P3AS05R509030DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	110	108	106	105	104	102		102	101	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91
4	100	94	89	85	99	92	88	85	90	87	84		88	85	83		87
5	96	89	84	80	94	88	83	79	86	82	79		84	81	78		83
6	92	84	79	75	91	83	78	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	70		77	73	70		76
8	84	76	71	67	83	76	71	67	75	70	67		74	69	66		73
9	81	73	67	64	80	72	67	64	71	67	63		70	66	63		70
10	78	69	64	61	77	69	64	61	68	64	60		67	63	60		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	242875
5°	236407
10°	225603
15°	204246
20°	176695
25°	144928
30°	83253
35°	25859
40°	6956
45°	2419
50°	580
55°	191
60°	88
65°	104
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2419 cd/sqm

TEST NUMBER: P1251290

CATALOG NUMBER: P3AS05R509030DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.6	14.5
10°-20°	249.3	35.9
20°-30°	262.0	37.7
30°-40°	75.0	10.8
40°-50°	7.3	1.1
50°-60°	0.6	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	611.9	88.0
0°-40°	686.9	98.8
0°-60°	694.8	100.0
0°-90°	694.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	694.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1108	
5°	1074	101
15°	900	249
25°	599	262
35°	97	75
45°	8	7
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1251290

CATALOG NUMBER: P3AS05R509030DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1107.6
1°	1105.9
2°	1101.0
3°	1093.9
4°	1084.3
5°	1074.0
6°	1063.0
7°	1051.2
8°	1040.2
9°	1027.4
10°	1013.2
11°	996.8
12°	977.9
13°	954.3
14°	928.8
15°	899.7
16°	868.8
17°	838.9
18°	808.2
19°	781.2
20°	757.2
21°	734.1
22°	707.9
23°	677.8
24°	642.4
25°	599.0
26°	552.0
27°	499.5
28°	447.3
29°	390.9
30°	328.8
31°	270.7
32°	217.3
32.5°	194.0
33°	170.4
34°	130.7
35°	96.6
36°	70.9
37°	52.7
37.5°	45.6
38°	39.5
39°	30.7
40°	24.3
42.5°	13.7
45°	7.8



TEST NUMBER: P1251290

CATALOG NUMBER: P3AS05R509030DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	4.4
50°	1.7
52.5°	0.7
55°	0.5
57.5°	0.5
60°	0.2
62.5°	0.2
65°	0.2
67.5°	0.2
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)