

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1250081

Luminaire Tested: P3AS20R509027D010 E3CD1MMS

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1250081  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-32)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R509027D010 E3CD1MMS  
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 90CRI , E3CD1MMS TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2160.0 lumens  
Efficiency: N/A  
Efficacy: 75.0 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.76  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1250081

CATALOG NUMBER: P3AS20R509027D010 E3CD1MMS

### Luminous Intensity Polar Plot



TEST NUMBER: P1250081

CATALOG NUMBER: P3AS20R509027D010 E3CD1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 114 | 112 | 109 | 107 | 112 | 109 | 107 | 106 | 105 | 104 | 102 |  | 102 | 101 | 99  |  | 98  |
| 2   | 109 | 105 | 101 | 98  | 107 | 103 | 100 | 97  | 100 | 97  | 95  |  | 97  | 95  | 93  |  | 94  |
| 3   | 105 | 99  | 95  | 91  | 103 | 98  | 94  | 90  | 95  | 92  | 89  |  | 93  | 90  | 88  |  | 91  |
| 4   | 100 | 94  | 89  | 85  | 99  | 92  | 88  | 85  | 90  | 87  | 84  |  | 88  | 85  | 83  |  | 87  |
| 5   | 96  | 89  | 84  | 80  | 94  | 88  | 83  | 79  | 86  | 82  | 79  |  | 84  | 81  | 78  |  | 83  |
| 6   | 92  | 84  | 79  | 75  | 91  | 83  | 79  | 75  | 82  | 78  | 74  |  | 81  | 77  | 74  |  | 79  |
| 7   | 88  | 80  | 75  | 71  | 87  | 79  | 74  | 71  | 78  | 74  | 71  |  | 77  | 73  | 70  |  | 76  |
| 8   | 85  | 76  | 71  | 67  | 83  | 76  | 71  | 67  | 75  | 70  | 67  |  | 74  | 70  | 67  |  | 73  |
| 9   | 81  | 73  | 68  | 64  | 80  | 72  | 67  | 64  | 71  | 67  | 64  |  | 71  | 66  | 63  |  | 70  |
| 10  | 78  | 69  | 64  | 61  | 77  | 69  | 64  | 61  | 68  | 64  | 61  |  | 68  | 63  | 61  |  | 67  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 752264 |
| 5°  | 738805 |
| 10° | 709383 |
| 15° | 650492 |
| 20° | 573607 |
| 25° | 439646 |
| 30° | 239049 |
| 35° | 76908  |
| 40° | 18062  |
| 45° | 2450   |
| 50° | 2149   |
| 55° | 2409   |
| 60° | 2061   |
| 65° | 2439   |
| 70° | 2052   |
| 75° | 2711   |
| 80° | 2020   |
| 85° | 4026   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 85°  
Luminance: 4026 cd/sqm

TEST NUMBER: P1250081

CATALOG NUMBER: P3AS20R509027D010 E3CD1MMS

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 315.0  | 14.6      |
| 10°-20°   | 796.5  | 36.9      |
| 20°-30°   | 797.7  | 36.9      |
| 30°-40°   | 224.3  | 10.4      |
| 40°-50°   | 13.5   | 0.6       |
| 50°-60°   | 5.1    | 0.2       |
| 60°-70°   | 4.1    | 0.2       |
| 70°-80°   | 2.7    | 0.1       |
| 80°-90°   | 1.1    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 1909.2 | 88.4      |
| 0°-40°    | 2133.5 | 98.8      |
| 0°-60°    | 2152.1 | 99.6      |
| 0°-90°    | 2160.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2160.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 3431 |      |
| 5°  | 3356 | 315  |
| 15° | 2865 | 797  |
| 25° | 1817 | 798  |
| 35° | 287  | 224  |
| 45° | 8    | 14   |
| 55° | 6    | 5    |
| 65° | 5    | 4    |
| 75° | 3    | 3    |
| 85° | 2    | 1    |
| 90° | 0    |      |

TEST NUMBER: P1250081

CATALOG NUMBER: P3AS20R509027D010 E3CD1MMS

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 3430.6 |
| 2.5°  | 3413.2 |
| 5°    | 3356.4 |
| 7.5°  | 3279.0 |
| 10°   | 3185.9 |
| 12.5° | 3045.4 |
| 15°   | 2865.4 |
| 17.5° | 2658.6 |
| 20°   | 2458.1 |
| 22.5° | 2208.7 |
| 25°   | 1817.1 |
| 27.5° | 1353.0 |
| 30°   | 944.1  |
| 32.5° | 569.9  |
| 35°   | 287.3  |
| 37.5° | 135.8  |
| 40°   | 63.1   |
| 42.5° | 23.7   |
| 45°   | 7.9    |
| 47.5° | 6.3    |
| 50°   | 6.3    |
| 52.5° | 6.3    |
| 55°   | 6.3    |
| 57.5° | 4.7    |
| 60°   | 4.7    |
| 62.5° | 4.7    |
| 65°   | 4.7    |
| 67.5° | 3.2    |
| 70°   | 3.2    |
| 72.5° | 3.2    |
| 75°   | 3.2    |
| 77.5° | 1.6    |
| 80°   | 1.6    |
| 82.5° | 1.6    |
| 85°   | 1.6    |
| 87.5° | 0.0    |
| 90°   | 0.0    |

(END OF REPORT)